




Connectors &gt; Rectangular Connectors &gt; Connector Contacts

Contact Type: **Pin**Contact Mating Area Plating Material: **Gold**Wire Contact Termination Area Plating Material: **Gold**Operating Voltage: **600 VDC**

## Features

### Product Type Features

Discrete Wire Type	Stranded
Glow Wire Rating	Standard Part - Not Glow Wire
Connector System	Wire-to-Wire
Connector & Contact Terminates To	Wire & Cable

### Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

### Electrical Characteristics

Operating Voltage	600 VDC
-------------------	---------

### Contact Features

Contact Diameter	.99 mm[.039 in]
Underplate Material Thickness	1.27 $\mu$ m[50 $\mu$ in]
Contact Mating Area Plating Thickness	.76 $\mu$ m[29.92 $\mu$ in]
Contact Underplating Material	Nickel
Contact Type	Pin



Contact Mating Area Plating Material	Gold
Wire Contact Termination Area Plating Material	Gold
Contact Retention Within Housing	Without
Contact Base Material	Brass
Contact Current Rating (Max)	10.5 A

### Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

### Mechanical Attachment

Connector Mounting Type	Cable Mount (Free-Hanging)
-------------------------	----------------------------

### Dimensions

Accepts Wire Insulation Diameter Range	1.19 – 1.75 mm [.047 – .069 in]
Wire Size	.12 – .4 mm <sup>2</sup>

### Usage Conditions

Operating Temperature Range	-20 – 105 °C [-4 – 221 °F]
-----------------------------	----------------------------

### Operation/Application

For Use With	Plug or Cap Housing
Circuit Application	Power

### Industry Standards

UL File Number	E28476
UL Rating	Recognized
UL Flammability Rating	UL 94V-0, UL 94V-2
Agency/Standard	CSA, UL
VDE Tested	Yes

### Packaging Features

Packaging Method	Bag/Box
Packaging Quantity	1000

### Other

Comment	These contacts can be used in either Mini-Universal MATE-N-LOK 2 Plug or Cap housings ONLY.
---------	---

### Product Compliance

For compliance documentation, visit the product page on [TE.com](https://www.te.com)>



EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) SVHC > Threshold: Pb (13% in Component Part) <b>Article Safe Usage Statements:</b> Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # 189727-1  
EXTRACTION TOOL



TE Part # 794215-1  
24P MINI UMNL2 CAP HSG UL94V0






TE Part # 794200-1  
12P MINI UMNL2 PLUG HSG MATRIX



TE Part # 794198-1  
12P MINI UMNL2 PLUG HSG DBLROW



## Also in the Series | Mini-Universal MATE-N-LOK 2



## Documents



### Product Drawings

[MINI UMNL2 PIN 26-22 AWG AU LP](#)

English

---

### CAD Files

Customer View Model

[ENG\\_CVM\\_794226-3\\_D.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_794226-3\\_D.3d\\_stp.zip](#)

English

Customer View Model

[ENG\\_CVM\\_794226-3\\_D.2d\\_dxf.zip](#)

English

[3D PDF](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

### Datasheets & Catalog Pages

[SOFT\\_SHELL\\_PIN\\_AND\\_SOCKET\\_CONNECTORS\\_CATALOG](#)

English

---

### Product Specifications

[Engineering Report](#)

English

---

### Product Environmental Compliance

[TE Material Declaration](#)

English