

794785-1 ✓ ACTIVE

MATE-N-LOK | Universal MATE-N-LOK

TE Internal #: 794785-1

Rectangular Connector Seals, Interface Seal, -67 – 221 °F [-55 – 105 °

C], Universal MATE-N-LOK

[View on TE.com >](#)



Connectors > Rectangular Connectors > Rectangular Connector Accessories > Rectangular Connector Seals



Connector Seal Type: **Interface Seal**

Operating Temperature Range: -55 – 105 °C [-67 – 221 °F]

Features

Product Type Features

Accessory Color	Black
Product Type	Accessory
Connector Seal Type	Interface Seal

Body Features

Material	Silicone Foam
Color	Black

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

For Use With	Universal MATE-N-LOK Sealed Connectors
--------------	--

Packaging Features

Packaging Method	Reel
Packaging Quantity	1000

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer












This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # 794271-1 03P UMNL INTERFACE SEAL</p>	 <p>TE Part # 794275-1 06P UMNL INTERFACE SEAL</p>	 <p>TE Part # 794994-1 09P UMNL BLACK INTERFACE SEAL</p>	 <p>TE Part # 794273-1 04P UMNL INTERFACE SEAL</p>
 <p>TE Part # 794269-1 02P UMNL INTERFACE SEAL</p>	 <p>TE Part # 794992-1 03P UMNL BLACK INTERFACE SEAL</p>	 <p>TE Part # 794991-1 02P UMNL BLACK INTERFACE SEAL</p>	 <p>TE Part # 794993-1 06P UMNL BLACK INTERFACE SEAL</p>



Also in the Series | Universal MATE-N-LOK



Documents

Product Drawings

04P UMNL INTERFACE SEAL

English

CAD Files

3D PDF

3D

Customer View Model



[ENG_CVM_CVM_794785-1_D_c-794785-1-d.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_794785-1_D_c-794785-1-d.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_794785-1_D_c-794785-1-d.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

[MATE-N-LOK Sealed Universal Connectors](#)

English