


Buchanan

TE Internal #: 796638-9

PCB Terminal Blocks, Header, Wire-to-Board, 9 Position, .2 in [5.08 mm] Centerline, 1 Row, 30 – 12 AWG Wire Size, .05 – 3 mm² Wire Size, 15 A, 300 VAC

[View on TE.com >](#)
[Connectors > Terminal Blocks & Strips > PCB Terminal Blocks](#)
Terminal Block Connector Type: **Header**Connector System: **Wire-to-Board**Number of Positions: **9**Centerline (Pitch): **5.08 mm [.2 in]**Number of Rows: **1**

Features

Product Type Features

| | |
|-----------------------------------|-----------------------|
| Block Type | PCB Mount |
| Header Type | Fully Shrouded |
| Terminal Block Connector Type | Header |
| Connector System | Wire-to-Board |
| Connector & Contact Terminates To | Printed Circuit Board |

Configuration Features

| | |
|---------------------|---------|
| Threaded Flange | Without |
| Closed End | With |
| Number of Positions | 9 |
| Number of Rows | 1 |

Electrical Characteristics

| | |
|----------------------|---------|
| Current Rating (Max) | 15 A |
| Voltage Rating | 300 VAC |

Body Features



| | |
|-----------|---------|
| Interlock | Without |
|-----------|---------|

Contact Features

| | |
|---------------------------------------|-----------------|
| Contact Mating Area Plating Material | Tin |
| Contact Mount | Through Hole |
| Contact Mating Area Plating Thickness | 6 – 7 μm |
| Contact Base Material | Phosphor Bronze |
| Contact Current Rating (Max) | 15 A |

Mechanical Attachment

| | |
|--------------------------|-------------|
| Mating Angle | 90° |
| Screwless Terminal Block | No |
| Mounting Angle | Right Angle |
| Screw Flange | Without |
| Connector Mounting Type | Board Mount |

Housing Features

| | |
|--------------------|-----------------|
| Housing Color | Green |
| Housing Material | PA 66 |
| Centerline (Pitch) | 5.08 mm [.2 in] |

Dimensions

| | |
|-----------------|-------------------------|
| PCB Tail Length | 3.5 mm [.138 in] |
| Wire Size | .05 – 3 mm ² |

Usage Conditions

| | |
|-----------------------------|-----------------------------|
| Operating Temperature Range | -40 – 105 °C [-40 – 221 °F] |
|-----------------------------|-----------------------------|

Operation/Application

| | |
|---------------------|----------------|
| Circuit Application | Power & Signal |
|---------------------|----------------|

Packaging Features

| | |
|--------------------|-----|
| Packaging Quantity | 100 |
|--------------------|-----|

Product Compliance

For compliance documentation, visit the product page on [TE.com](https://www.te.com)>

| | |
|------------------------------|-----------|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Compliant |







| | |
|---|---|
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC |
| Halogen Content | Not Yet Reviewed for halogen content |
| Solder Process Capability | Wave solder capable to 265°C |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

| | | | |
|---|---|--|--|
|  <p>TE Part # 796634-9 9 POS 5.08MM R/A PLUG,TRM BLK</p> |  <p>TE Part # 284047-9 TERMI-BLOK VERTICAL PLUG STACK</p> |  <p>TE Part # 1986262-9 9 POS PLUG SPRING CONN, PITCH 5.08</p> |  <p>TE Part # 284041-9 TERMINAL BLK VERTICAL PLUG STA</p> |
|  <p>TE Part # 4-796634-9 9 POS 5.08MM R/A PLUG,TRM BLK, Marked</p> |  <p>TE Part # 4-796635-3 9 POS 5.08MM R/A PLUG,TRM BLK, AU</p> |  <p>TE Part # 4-796635-6 9 POS 5.08MM R/A PLUG,TRM BLK, Spld Mark</p> |  <p>TE Part # 796635-9 9 POS 5.08MM R/A PLUG,TRM BLK</p> |

Documents

Product Drawings

9POS 5.08MM CE R/A HDR,TRM BLK

English



CAD Files

Customer View Model

[ENG_CVM_796638-9_C3.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_796638-9_C3.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_796638-9_C3.2d_dxf.zip](#)

English

3D PDF

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_796638-9_C.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_796638-9_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_796638-9_C.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[BUCHANAN TERMINAL BLOCKS CATALOG - EUROSTYLE TERMINAL BLOCKS](#)

English

[BUCHANAN PCB TERMINAL BLOCKS](#)

English

[1-1773458-1_EURO_STYLE_TERMINAL_BLOCKS_QRG](#)

English

Product Specifications

[Application Specification](#)

English