



Connectors > Socket Connectors > Memory Sockets > SIMM Sockets



Module Orientation: **Right Angle**

Number of Positions: **72**

Centerline (Pitch): **1.27 mm [.05 in]**

Connector & Contact Terminates To: **Printed Circuit Board**

Contact Current Rating (Max): **1 A**

Features

Product Type Features

Connector & Contact Terminates To	Printed Circuit Board
-----------------------------------	-----------------------

Configuration Features

Number of Keys	1
Number of Rows	1
Module Orientation	Right Angle
Number of Positions	72

Body Features

Latch Material	Brass
Retention Post Location	Center
Latch Plating Material	Nickel
Connector Profile	Standard

Contact Features

Memory Socket Type	Memory Card
	30 µin
Contact Mating Area Plating Material	Gold
Contact Underplating Material	Nickel
PCB Contact Termination Area Plating Material	Tin
Contact Base Material	Phosphor Bronze
Contact Current Rating (Max)	1 A



Termination Features

Insertion Style	Cam-In
Termination Post & Tail Length	3.05 mm[.12 in]

Mechanical Attachment

Polarization	Left
Mating Alignment Type	Center Post
PCB Mounting Style	Through Hole - Solder
Connector Mounting Type	Board Mount

Housing Features

Housing Material	LCP (Liquid Crystal Polymer)
Centerline (Pitch)	1.27 mm[.05 in]

Dimensions

Center Retention Hole Diameter	2.45 mm[.096 in]
--------------------------------	------------------

Usage Conditions

Operating Temperature Range	-55 – 85 °C[-67 – 185 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Quantity	24
Packaging Method	Box & Tray, Tray

Product Compliance

For compliance documentation, visit the product page on [TE.com](https://www.te.com)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Wave solder capable to 240°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | MICRO-EDGE SIMM



SIMM Sockets(3)

Documents

Product Drawings

SIMM II,.160"H,.050CL,72P,AU

English

CAD Files

Customer View Model

ENG_CVM_7-5382483-2_A.3d_igs.zip

English

Customer View Model

ENG_CVM_7-5382483-2_A.3d_stp.zip

English

Customer View Model

ENG_CVM_7-5382483-2_A.2d_dxf.zip

English

3D PDF

English

7-5382483-2

SIMM Sockets, Right Angle Module Orientation, 72 Position, -67 – 185 °F [-55 – 85 °C], MICRO-EDGE SIMM



By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.