




Relays, Contactors & Switches > Relays > Mil-Aero Relays > Mid-Range Relays



Mid-Range Relay Contact Arrangement: **4 Form C, 4PDT, 4 C/O**

Coil Suppression Diode: **With**

Auxiliary Contacts: **Without**

Terminal Plating: **Tin-Lead**

Mid-Range Relay Contact Current Rating: **5 A**

Features

Product Type Features

Enclosure Type	Hermetically Sealed
Terminal Configuration	Solder Pins
Product Type	Relay
Relay Type	Military/Aerospace Mid-Range

Electrical Characteristics

Vibration	30G's, 70 – 3000Hz
Shock	200G's, 6ms
Coil Suppression Diode	With
Mid-Range Relay Coil Voltage Rating	28 VDC
Mid-Range Relay Coil Resistance	400 Ω
Back EMF Suppression	With
Coil Magnetic System	Polarized, Monostable
Actuating System	DC

Contact Features

Mid-Range Relay Contact Arrangement	4 Form C, 4PDT, 4 C/O
Auxiliary Contacts	Without
Terminal Plating	Tin-Lead
Mid-Range Relay Contact Current Rating	5 A



Contact Base Material	Silver Cadmium Oxide
-----------------------	----------------------

Mechanical Attachment

Mid-Range Relay Mounting Type	Raised Vertical Flange Mount
-------------------------------	------------------------------

Usage Conditions

Operating Temperature Range	-70 – 125 °C
-----------------------------	--------------

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not lead free process capable


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # 5-1617758-2
FCB-205-0226M=M83536/2-026M




TE Part # 4-1617758-8
FCB-205-0223M=M83536/2-023M




TE Part # 3-1617758-5
FCB-205-0125M=M83536/1-025M



TE Part # 4-1617758-9
FCB-205-0224L=M83536/2-024L



TE Part # 8-1617758-1
FCB-205-CX3



TE Part # 9-1617758-0
FCB-205-HX4



TE Part # 1-1617785-0
FCB-205-0132L=M83536/1-032L



TE Part # 1-1617785-6
FCB-205-0135L=M83536/1-035L



TE Part # 1617785-3
FCB-205-0128M=M83536/1-028M



TE Part # 1617785-9
FCB-205-0131M=M83536/1-031M



TE Part # 2-1617786-3
FCB-205-0201M=M83536/2-001M



TE Part # 2-1617786-9
FCB-205-0205L=M83536/2-005L



TE Part # 3-1617786-1
FCB-205-0206L=M83536/2-006L



TE Part # 3-1617786-7
FCB-205-0210L=M83536/2-010L



TE Part # 4-1617786-2
FCB-205-0215M=M83536/2-015M



TE Part # 4-1617786-3
FCB-205-0213M=M83536/2-013M



TE Part # 4-1617786-9
FCB-205-0217L=M83536/2-017L



TE Part # 5-1617786-3
FCB-205-0221L=M83536/2-021L



TE Part # 5-1617786-9
FCB-205-0228L=M83536/2-028L



TE Part # 6-1617777-3
FCB-205-0107L M83536/1-007L RELAY

Also in the Series | CII FCB-405 Series



Documents

Product Drawings

FCB-405-0620M=M83536/6-020M

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_8-1617760-0_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_8-1617760-0_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_8-1617760-0_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

5-1773450-5_sec5_FCB-405

English