




Connectors > D-Shaped Connectors > D-Sub Accessories > D-Sub Connector Boots



Boot Angle: **Straight**

Adhesive Pre-Coating: **Without**

Adhesive Description: **Adhesive Purchased Separately**

Number of Positions: **0**

Centerline (Pitch): **0 mm [0 in]**

Features

Product Type Features

| | |
|----------------------|-------------------------------|
| Product Type | Molded Boot |
| Molded Part Type | D Subminiature Boot |
| Adhesive Description | Adhesive Purchased Separately |

Configuration Features

| | |
|---------------------|---|
| Number of Positions | 0 |
|---------------------|---|

Body Features

| | |
|-----------------------|--------------------------------|
| Material Systems Code | 10 |
| Material | Semi rigid Modified Polyolefin |
| Material Code | 3 |
| Boot Angle | Straight |
| Adhesive Pre-Coating | Without |

Contact Features

| | |
|------------------------------|-----|
| Contact Current Rating (Max) | 0 A |
|------------------------------|-----|

Housing Features

| | |
|--------------------|------------|
| Centerline (Pitch) | 0 mm[0 in] |
|--------------------|------------|

Dimensions

| | |
|------------------|------------------|
| Connector Length | 28 mm |
| Connector Width | 10.7 mm[.421 in] |



Usage Conditions

| | |
|-----------------------------|----------------------------|
| Operating Temperature Range | -55 – 135 °C[-67 – 275 °F] |
|-----------------------------|----------------------------|

Other

| | |
|------------------|---|
| Adhesive Code | S1125 |
| Comment | Contact Raychem for additional adhesive and/or cut off boot length information |
| Adhesive Options | S1006 Separate Adhesive, S1017 Separate Adhesive, S1030 Separate Adhesive, S1048 Separate Adhesive, S1125 Separate Adhesive |

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

| | |
|---|---|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC |
| Halogen Content | Not Low Halogen - contains Br or Cl > 900 ppm. |
| Solder Process Capability | Not applicable for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Documents

Product Drawings

[214A021-3-0](#)

English

Datasheets & Catalog Pages

[1654025_Sec4_-3](#)

English

[Raychem Molded Parts Visual Guide](#)

English

Product Specifications

[Product Specification](#)

English

Product Environmental Compliance

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

English

[Safety Datasheet](#)

French

[Safety Datasheet](#)

German

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)