

929968-1 ✓ ACTIVE

AMP | Round Connector System


TE Internal #: 929968-1

Automotive Terminals, Pin, Pin Diameter .098 in [2.5 mm], 17 – 13 AWG Wire Size, 1 – 2.5 mm<sup>2</sup> Wire Size, Sealable, Round Connector System

[View on TE.com >](#)



Terminals & Splices > Automotive Terminals > ROUND CONNECTOR SYSTEM, PIN AND SOCKET



Terminal Type: Pin

Mating Pin Diameter: 2.5 mm [.098 in]

Terminal Transmits: 25 – 40 A (Power)

Wire Size: 1 – 2.5 mm<sup>2</sup>

[All Round Connector System, Pin and Socket \(74\)](#)

### Features

#### Product Type Features

Sealable	Yes
Primary Locking Feature	Locking Lance

#### Body Features

Terminal Seal Type	Single Wire Seal (SWS)
--------------------	------------------------

#### Contact Features

Contact Size	2.5mm
Contact Fabrication	Stamped & Formed
Typical Current Rating	34 A
Crimp Type	F-Crimp
Terminal Type	Pin
Mating Pin Diameter	2.5 mm[.098 in]
Interface Plating	Tin (Sn)
Contact Termination Area Plating Material	Tin (Sn)

#### Termination Features

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire

#### Dimensions



Wire Size	1 – 2.5 mm <sup>2</sup>
Wire Size Search	13 AWG, 14 AWG, 15 AWG, 16 AWG, 17 AWG
Wire Insulation Diameter	2.2 – 3 mm [.086 – .118 in]

### Usage Conditions

Insulation Option	Uninsulated
Operating Temperature (Max)	80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C, 125 °C, 130 °C [176 °F][185 °F][194 °F][212 °F][221 °F][230 °F][248 °F][257 °F][266 °F]
Operating Temperature Range	-40 – 130 °C [-40 – 266 °F]

### Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

### Packaging Features

Packaging Method	Carton
Packaging Quantity	3000

### Other

Terminal Transmits	25 – 40 A (Power)
--------------------	-------------------

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent

chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts




TE Part # CAT-C4962-CH8172  
CIRCULAR DIN HOUSINGS



TE Part # 58606-1  
PROCRIMP 1.5 & 2.5MM PIN/SEAL



TE Part # 1-1579007-8  
EXTRACTION TOOL



TE Part # 828921-1  
EINZELADERDICHTUNG



TE Part # 2305570-1  
Strip Terminal Cutter-Side Feed-No Crimp



TE Part # 3-1579007-2  
INSERTION TOOL



TE Part # 2-2151345-1  
OCEAN\_2.0\_APPLICATOR-S-100F1700



TE Part # 2-2151345-2  
OCEAN\_2.0\_APPLICATOR-S-100F1700



TE Part # 2151345-1  
OCEAN\_2.0\_APPLICATOR-S-100F1700



TE Part # 2151345-2  
OCEAN\_2.0\_APPLICATOR-S-100F1700



TE Part # 5-2151345-1  
OCEAN\_2.0\_APPLICATOR-S-100F1700



TE Part # 5-2151345-2  
OCEAN\_2.0\_APPLICATOR-S-100F1700



TE Part # 58606-2  
PC DIE 1.5 & 2.5 PIN W/S



TE Part # 7-2151345-1  
OCEAN\_2.0\_APPLICATOR-S-100F1700








TE Part # 7-2151345-2  
OCEAN\_2.0\_APPLICATOR-S-100F1700



TE Part # 7-2151345-7  
OCEAN\_2.0\_SPARE\_PART\_KIT-100F1700



## Also in the Series | Round Connector System



## Documents

### Product Drawings

#### 2,5MM PIN CONTACT

English

#### 2,5MM PIN CONTACT

German

### CAD Files

Customer View Model

[ENG\\_CVM\\_929968-1\\_A2.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_929968-1\\_A2.3d\\_stp.zip](#)

English

Customer View Model

[ENG\\_CVM\\_929968-1\\_A2.2d\\_dxf.zip](#)

English



### 3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

#### CONNECTOR SELECTOR

English

### Product Specifications

#### Application Specification

English

#### Application Specification

English