

HFT5000-34/17-0-SP ✓ ACTIVE

RAYCHEM | RAYCHEM HFT5000

TE Internal #: 9615924003

Heat Shrink Tubing, Black, Fiber & Fabric Wall Material, 1.339 in [34 mm] Expanded Inside, .669 in [17 mm] Recovered Inside, RAYCHEM HFT5000

[View on TE.com >](#)



Heat Shrink Tubing



Primary Product Color: **Black**

Wall Material Type: **Fiber & Fabric**

Expanded Inside Diameter (Min): **34 mm [1.339 in]**

Recovered Inside Diameter (Max): **17 mm [.669 in]**

Shrink Ratio: **2:1**

Features

Product Type Features

Product Family	HFT5000
Wall Material Type	Fiber & Fabric

Body Features

Fluid Type	Antifreeze, Battery Acid, Brake Fluid, Car Wash Detergent, Diesel Fuel, Hydraulic Fluid, Lubricating Oil, Unleaded Gasoline
Primary Product Color	Black
Shrink Ratio	2:1
Primary Product Material	Polyethylene/Polyester
Flexibility	Very Flexible

Dimensions

Expanded Inside Diameter (Min)	34 mm[1.339 in]
Recovered Inside Diameter (Max)	17 mm[.669 in]
Heat Shrink Tubing Size Range	17 – 34 mm[.669 – 1.339 in]

Usage Conditions

Shrink Temperature (Min)	80 °C
Fluid Resistance	None
Heat Shrink Tubing Flammability	Non-Flame-Retardant
Operating Temperature Range	-40 – 125 °C



Heat Shrink Tubing Resistance	Abrasion, Cut-Through, Mechanical Damage
-------------------------------	--

Recovery Temperature	110 °C
----------------------	--------

Product Availability

Applicable Region	Global
-------------------	--------

Packaging Features

Packaging Method	Reel
------------------	------

Other

Product Source	Czech Republic
----------------	----------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
--	---

Halogen Content	Out of Scope - excluded from Halogen requirements
-----------------	---

Solder Process Capability	Not applicable for solder process capability
---------------------------	--

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # CJ2087-000
HL2010E-KIT-120V



TE Part # EG1114-000
CV1981-ST-230V1600W-EU

Also in the Series | RAYCHEM HFT5000



Heat Shrink Tubing(241)

Documents

Datasheets & Catalog Pages

[HFT5000 Pages from 9-1773447-9](#)

English

Measuring_Single_Wall_Tubing

English

Selecting_Correct_Tubing

English

Product Specifications

Quality Specification

English

Agency Approvals

UL

English