




AMP | Micro Timer II

TE Internal #: 962876-2

Automotive Terminals, Receptacle, Mating Tab Width .063 in [1.6 mm], Tab Thickness .024 in [.6 mm], 20 – 17 AWG Wire Size, Micro Timer II

[View on TE.com >](#)

Terminals & Splices > Automotive Terminals > TIMER, RECEPTACLE AND TAB



Terminal Type: **Receptacle**

Mating Tab Width: **1.6 mm [ .063 in ]**

Mating Tab Thickness: **.6 mm [ .024 in ]**

Terminal Transmits: **0 – 24 A (Low Power)**

Wire Size: **20 – 17 AWG**

[All TIMER, RECEPTACLE AND TAB \(332\)](#)

**Features**

**Product Type Features**

Sealable	Yes
Primary Locking Feature	Locking Lance

**Body Features**

Terminal Seal Type	Single Wire Seal (SWS)
--------------------	------------------------

**Contact Features**

Contact Size	1.6mm
Contact Fabrication	Stamped & Formed
Typical Current Rating	10 A
Crimp Type	F-Crimp
Terminal Type	Receptacle
Mating Tab Width	1.6 mm[.063 in]
Mating Tab Thickness	.6 mm[.024 in]
Interface Plating	Tin (Sn)
Contact Termination Area Plating Material	Tin (Sn)

**Termination Features**

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire



### Dimensions

Wire Size	.5 – 1 mm <sup>2</sup>
Wire Size Search	17 AWG, 18 AWG, 19 AWG, 20 AWG
Wire Insulation Diameter	1.4 – 2.1 mm, 2.8 mm [.11 in]

### Usage Conditions

Insulation Option	Uninsulated
Operating Temperature (Max)	80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C [176 °F][185 °F][194 °F][212 °F][221 °F][230 °F][248 °F]
Operating Temperature Range	-40 – 120 °C [-40 – 248 °F]

### Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

### Industry Standards

Agency/Standard	IEC 664/664A (DIN VDE 0110)
-----------------	-----------------------------

### Packaging Features

Packaging Method	Reel
Packaging Quantity	4000

### Other

Terminal Transmits	0 – 24 A (Low Power)
--------------------	----------------------

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # 539960-1  
AUSZ-WKZ,MICRO TIM.



TE Part # 964972-1  
EINZELLEITERDICHTNG



TE Part # 963530-1  
EINZELLEITERDICHTNG



TE Part # 2305570-1  
Strip Terminal Cutter-Side Feed-No Crimp



TE Part # CAT-T4827-CH8172  
TIMER, CONNECTOR HOUSING



TE Part # 5-1579018-6  
INSERTION TOOL



TE Part # 1-284716-3  
6 POS REC. CONNECTOR FOR MTII



TE Part # 2-2151170-1  
OCEAN-2.0-APPLICATOR-S-080F1300



TE Part # 2-2151170-2  
OCEAN-2.0-APPLICATOR-S-080F1300



TE Part # 2151170-1  
OCEAN-2.0-APPLICATOR-S-080F1300



TE Part # 2151170-2  
OCEAN-2.0-APPLICATOR-S-080F1300



TE Part # 5-2151170-1  
OCEAN-2.0-APPLICATOR-S-080F1300



TE Part # 7-2151170-1  
OCEAN-2.0-APPLICATOR-S-080F1300



TE Part # 7-2151170-2  
OCEAN-2.0-APPLICATOR-S-080F1300



TE Part # 7-2151170-7  
OCEAN\_2.0\_SPARE\_PART\_KIT-080F1300



TE Part # 7-2266059-7  
OC-080F1300-CRIMP TOOLINGKIT



TE Part # 2393336-2  
SDE F MICRO TIMER 22-17 DIE SET



TE Part # 2393336-1  
SDE F MICRO TIMER 22-17 ASSY




TE Part # 1-284716-1  
6 POS REC. CONNECTOR FOR EGR V




TE Part # 1-284716-2  
6 POS REC. CONNECTOR FOR EGAS


## Also in the Series | Micro Timer II




Automotive Connector Caps & Covers  
(2)




Automotive Connector Locks &  
Position Assurance(1)




Automotive Housings(29)



Automotive Seals & Cavity Plugs(1)



Automotive Terminals(28)



Insertion & Extraction Tools(4)

## Documents

### Product Drawings

[MT2 REC 1.6 Contact SWS Sn](#)

English

### CAD Files

Customer View Model

[ENG\\_CVM\\_962876-2\\_N1.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_962876-2\\_N1.3d\\_stp.zip](#)

English

Customer View Model

[ENG\\_CVM\\_962876-2\\_N1.2d\\_dxf.zip](#)

English

### 3D PDF

3D



By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

## Datasheets & Catalog Pages

### Timer Interconnection System

English

---

## Product Specifications

### Application Specification

German

### Application Specification

English

### Application Specification

English