




AMP | Timer Connector System

TE Internal #: 964308-1

Automotive Terminals, Tab, Mating Tab Width .228 in [5.8 mm], Tab Thickness .031 in [.8 mm], 13 – 11 AWG Wire Size, Timer Connector System

[View on TE.com >](#)

Terminals & Splices > Automotive Terminals > TIMER, RECEPTACLE AND TAB



Terminal Type: **Tab**

Mating Tab Width: **5.8 mm [.228 in]**

Mating Tab Thickness: **.8 mm [.031 in]**

Terminal Transmits: **25 – 40 A (Power)**

Wire Size: **13 – 11 AWG**

[All TIMER, RECEPTACLE AND TAB \(332\)](#)

Features

Product Type Features

Receptacle Style	180°
Sealable	No
Primary Locking Feature	Locking Lance

Contact Features

Contact Size	5.8mm
Contact Fabrication	Stamped & Formed
Typical Current Rating	40 A
Crimp Type	F-Crimp
Terminal Type	Tab
Mating Tab Width	5.8 mm[.228 in]
Mating Tab Thickness	.8 mm[.031 in]
Interface Plating	Tin (Sn)
Contact Termination Area Plating Material	Tin (Sn)

Termination Features

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire

Dimensions



Wire Size	2.5 – 4 mm ²
Wire Size Search	11 AWG, 12 AWG, 13 AWG
Tab Length	25.2 mm[.992 in]
Wire Insulation Diameter	3.3 – 4.5 mm[.129 – .177 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature (Max)	80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C, 125 °C, 130 °C[176 °F][185 °F][194 °F][212 °F][221 °F][230 °F][248 °F][257 °F][266 °F]
Operating Temperature Range	-40 – 130 °C[-40 – 266 °F]

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Packaging Features

Packaging Method	Reel
Packaging Quantity	1700

Other

Terminal Transmits	25 – 40 A (Power)
--------------------	-------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2305570-1
Strip Terminal Cutter-Side Feed-No Crimp



TE Part # CAT-T4827-CH8172
TIMER, CONNECTOR HOUSING



TE Part # CAT-M9194-CH8172
MULTILOCK, CONNECTOR HOUSING



TE Part # CAT-T319-CH8172
TH/.025 CONNECTOR SYSTEM, HOUSING



TE Part # 2-2151150-1
OCEAN_2.0_APPLICATOR-S-130F180OV



TE Part # 2-2151150-2
OCEAN_2.0_APPLICATOR-S-130F180OVA



TE Part # 2151150-1
OCEAN_2.0_APPLICATOR-S-130F180OV



TE Part # 2151150-2
OCEAN_2.0_APPLICATOR-S-130F180OVA



TE Part # 2381114-1
SDE F AMP MCP 6.3/4.8K 4.0-6.0mm2 ASSY



TE Part # 2381114-2
SDE F AMP MCP 6.3/4.8K 4-6mm2 DIE SET



TE Part # 7-2151150-1
OCEAN_2.0_APPLICATOR-S-130F180OV



TE Part # 7-2151150-2
OCEAN_2.0_APPLICATOR-S-130F180OVA




TE Part # 7-2151150-7
OCEAN_2.0_SPARE_PART_KIT-130F180OV

Also in the Series | Timer Connector System



Automotive Connector Caps & Covers (11)




Automotive Connector Locks & Position Assurance (16)



Automotive Housings (218)



Automotive Seals & Cavity Plugs (31)



Automotive Terminals (130)




Crimp Terminal Housings (13)




Insertion & Extraction Tools (20)



Other Automotive Connector Accessories (1)



PCB Headers & Receptacles (78)



Quick Disconnects (4)

Documents

Product Drawings

[TAB A 5.8x0.8 CONTACT CF SRC Sn](#)

English

[TAB A 5.8x0.8 CONTACT CF SRC Sn](#)

English

CAD Files

[3D PDF](#)

3D

[Customer View Model](#)

[ENG_CVM_CVM_964308-1_A.2d_dxf.zip](#)

English

[Customer View Model](#)

[ENG_CVM_CVM_964308-1_A.3d_igs.zip](#)

English

[Customer View Model](#)



[ENG_CVM_CVM_964308-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

[Datasheets & Catalog Pages](#)

[Timer Interconnection System](#)

English

[Product Specifications](#)

[Application Specification](#)

German

[Application Specification](#)

English