

D-110-0181 ✓ ACTIVE

RAYCHEM

TE Internal #: 992899-000

Splices, 3600 – 6000 CMA Wire Size, Length 38.1 mm [1.5 in], Box,
Closed, Fully Insulated

[View on TE.com >](#)



Terminals & Splices > Splices



Sealable: **No**

Accepts Wire Insulation Diameter Range: **4.5 mm [.175 in]**

Wire Size: **3600 – 6000 CMA**

Serrated: **No**

Overall Product Length: **38.1 mm [1.5 in]**

Features

Product Type Features

| | |
|----------|----|
| Sealable | No |
| Serrated | No |

Body Features

| | |
|------------------|-------|
| Weight per Piece | .28 g |
|------------------|-------|

Contact Features

| | |
|-------------|--------|
| Barrel Type | Closed |
|-------------|--------|

Termination Features

| | |
|--------------------|--------|
| Termination Method | Solder |
|--------------------|--------|

Dimensions

| | |
|--|-----------------|
| Accepts Wire Insulation Diameter Range | 4.5 mm[.175 in] |
| Wire Size | 3600 – 6000 CMA |
| Overall Product Length | 38.1 mm[1.5 in] |

Usage Conditions

| | |
|-------------------|-----------------|
| Insulation Option | Fully Insulated |
|-------------------|-----------------|

Operation/Application

| | |
|------------|----|
| Heavy Duty | No |
|------------|----|

Industry Standards

| | |
|-----------------------------|----|
| Government Qualified Splice | No |
|-----------------------------|----|



Packaging Features

| | |
|--------------------|-----|
| Packaging Quantity | 500 |
| Packaging Method | Box |

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

| | |
|---|--|
| EU RoHS Directive 2011/65/EU | Not Compliant |
| EU ELV Directive 2000/53/EC | Not Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUL 2021 (219) SVHC > Threshold: Pb (32% in Solder) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location. |
| Halogen Content | Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free |
| Solder Process Capability | Not applicable for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CJ2087-000
HL2010E-KIT-120V

Documents

Product Drawings

[D-110-0181](#)

English

Datasheets & Catalog Pages

[1654025_Sec8_B-155_CWT_D-110_D-1744](#)

English

[Raychem Electrical Interconnect Products](#)

English

Product Specifications

[Product Specification](#)

English