



Connectors > RF Coax Connectors > RF Coax Accessories > Ferrules



Compatible With RF Cable Type: 21-598, RG 179, RG 179A, RG 187, RG 188

Ferrule Material: **Copper Alloy**

Ferrule Plating Material: **Silver**

Accepts Wire Insulation Diameter Range: 3.05 mm [.12 in]

Features

Product Type Features

| | |
|-------------------------------|---|
| Compatible With RF Cable Type | 21-598, RG 179, RG 179A, RG 187, RG 188 |
|-------------------------------|---|

Body Features

| | |
|-----------------------|--------|
| Body Plating Material | Silver |
|-----------------------|--------|

Contact Features

| | |
|--------------------------|--------------|
| Ferrule Material | Copper Alloy |
| Ferrule Plating Material | Silver |

Dimensions

| | |
|--|------------------|
| Accepts Wire Insulation Diameter Range | 3.05 mm [.12 in] |
|--|------------------|

Packaging Features

| | |
|------------------|---------|
| Packaging Method | Package |
|------------------|---------|

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

| | |
|---|--------------------------------------|
| EU RoHS Directive 2011/65/EU | Compliant with Exemptions |
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | Restricted Materials Above Threshold |

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2022
(224)Candidate List Declared Against: JUL 2021
(219)

SVHC > Threshold:

Pb (3.7% in Component Part)

Article Safe Usage Statements:

Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per
homogenous material. Also BFR/CFR/PVC
Free

Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts**Documents****Product Drawings**

FERRULE, STEP DOWN, PLTD

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_9-328666-3_BH.2d_dxf.zip

English



Customer View Model

[ENG_CVM_CVM_9-328666-3_BH.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_9-328666-3_BH.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Environmental Compliance

[Product Compliance](#)

English

[Product Compliance](#)

English

Agency Approvals

[Agency Approval Document](#)

English