

# VERSAFIT-KIT-6-0 ✓ ACTIVE

RAYCHEM | RAYCHEM Versafit

TE Internal #: C72402-000

Heat Shrink Tubing, Black, Single Wall, 4.1 in [104.14 mm]

Expanded Inside, 2 in [50.8 mm] Recovered Inside, 2:1 Shrink Ratio,

RAYCHEM Versafit

[View on TE.com >](#)



Heat Shrink Tubing



Primary Product Color: **Black**

Wall Type: **Single**

Expanded Inside Diameter (Min): **104.14 mm [ 4.1 in ]**

Recovered Inside Diameter (Max): **50.8 mm [ 2 in ]**

Shrink Ratio: **2:1**

## Features

### Product Type Features

Product Family	VERSAFIT
Wall Type	Single

### Electrical Characteristics

Voltage (Max)	.6 kV
---------------	-------

### Body Features

Fluid Type	Aviation Fuel, Chemicals/Solvents, De-Icing Fluid, Hydraulic Fluid, Lubricating Oil, Water
Primary Product Color	Black
Shrink Ratio	2:1
Primary Product Material	Irradiated Modified Polyolefin
Flexibility	Very Flexible

### Dimensions

Cut Length	152.4 mm[6 in]
Expanded Inside Diameter (Min)	104.14 mm[4.1 in]
Recovered Inside Diameter (Max)	50.8 mm[2 in]
Heat Shrink Tubing Size Range	50.8 – 104.14 mm[2 – 4.1 in]

### Usage Conditions

--	--



Shrink Temperature (Min)	70 °C
Fluid Resistance	Splash Protection
Heat Shrink Tubing Flammability	Highly Flame-Retardant
Operating Temperature Range	-55 – 135 °C
Heat Shrink Tubing Resistance	Fluids, Strain Relief, Wrinkling
Recovery Temperature	90 °C

**Product Availability**

Applicable Region	Global
-------------------	--------

**Packaging Features**

Packaging Method	Box
------------------	-----

**Other**

Meets Low Outgassing Requirements	No
Product Source	UK, US

**Product Compliance**

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on

requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts




TE Part # CJ2087-000  
HL2010E-KIT-120V



TE Part # EG1114-000  
CV1981-ST-230V1600W-EU

## Also in the Series | RAYCHEM Versafit



Heat Shrink Tubing(203)

## Documents

### Datasheets & Catalog Pages

[Tubing Kits Pages from 9-1773447-9](#)

English

[Measuring\\_Single\\_Wall\\_Tubing](#)

English

[Selecting\\_Correct\\_Tubing](#)

English

### Product Specifications

[Quality Specification](#)

English

### Product Environmental Compliance

[Safety Datasheet](#)

English

[Safety Datasheet](#)

English

[Safety Datasheet](#)

[Safety Datasheet](#)



[Safety Datasheet](#)

English

[Safety Datasheet](#)

French

[Safety Datasheet](#)

German

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

English

[Safety Datasheet](#)