




Connectors > PCB Connectors > PCB Connector Accessories > PCB Connector Keying



Connector Keying Accessory Type: **Keying Plug**

Keying Hardware Type: **External Key**

Sealable: **No**

Operating Temperature Range: **-65 – 105 °C [-85 – 221 °F]**

Features

Product Type Features

Connector Keying Accessory Type	Keying Plug
Sealable	No

Body Features

Primary Product Color	Natural
Keying Hardware Type	External Key

Usage Conditions

Operating Temperature Range	-65 – 105 °C[-85 – 221 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Box
Packaging Quantity	10000

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	



Current ECHA Candidate List: JUNE 2022 (224)
Candidate List Declared Against: JUNE 2022 (224)
Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 280514 AMPMODU II REC. HSG, SINGLE ROW, 12 POS.	 TE Part # 280366 AMPMODU II REC. HSG DUAL ROW, 16 POS.	 TE Part # 280365 AMPMODU, DBL ROW, CONTACT REC	 TE Part # 280515 AMPMODU II REC. HSG, DUAL ROW, 24 POS.
 TE Part # 280360 AMPMODU II REC. HSG, SINGLE ROW 6 POS	 TE Part # 280513 AMPMODU II REC. HSG, DUAL ROW, 18 POS	 TE Part # 280359 AMPMODU II REC. HSG, SINGLE ROW, 4 POS.	 TE Part # 280368 AMPMODU II REC. HSG, DUAL ROW, 30 POS.



TE Part # 280363
AMPMODU II REC. HSG, SINGLE ROW, 15 POS.



TE Part # 284123-1
AMPMODU II REC. HSG, DUAL ROW, 10 POS.



TE Part # 280362
AMPMODU II REC. HSG, SINGLE ROW, 10 POS.



TE Part # 280358
AMPMODU II REC. HSG, SINGLE ROW 2 POS



TE Part # 280512
AMPMODU II REC. HSG, SINGLE ROW, 9 POS.



TE Part # 281018
AMPMODU II REC. HSG, DUAL ROW, 36 POS.



TE Part # 280361
AMPMODU II REC. HSG, SINGLE ROW 8 POS



TE Part # 280364
AMPMODU II COSI REC. HSG, SGL ROW, 22POS




TE Part # 280369
AMPMODU II REC. HSG, DUAL ROW, 44 POS.

Also in the Series | AMPMODU IV/V



Automotive Housings(2)



Backplane Connector Housings(1)



Board-to-Board Connector Contacts(6)



Insertion & Extraction Tools(4)



PCB Connector Covers(18)



PCB Connector Keying(6)



PCB Connector Mounting(1)



PCB Connector Strain Relief(3)



PCB Headers & Receptacles(939)



PCB Latches, Locks & Retainers(7)



Rectangular Connector Housings(5)



Standard Rectangular Connectors(8)



Wire-to-Board Connector Assemblies & Housings(467)



Wire-to-Board Connector Contacts (326)

Documents

Product Drawings

MOD IV KEYING PLUG

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_87077-2_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_87077-2_C.3d_igs.zip

English

Customer View Model

ENG_CVM_87077-2_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

AMPMODU_INTERCONNECTION_SYSTEM_SECTION5_CONT

English

1-1773720-9_AMPMODU_MOD_IV_V_QRG

English

Product Specifications

Product Specification

English



Product Environmental Compliance

[MD_87077-2_031620181253_dmtec](#)

English

[MD_87077-2_031620181253_dmtec](#)

English