



Wire Protection & Management > Heat Shrink Shapes > Sealing Sleeves



Sealing Sleeve Product Type: **Heat Shrink Repair Sleeve**

Adhesive Inside Diameter: **2.13 mm [.084 in]**

Sleeve Inside Diameter: **3.43 mm [.135 in]**

Primary Product Color: **Blue**

Wire Size: **18 – 16 AWG**

Features

Product Type Features

Sealing Sleeve Product Type	Heat Shrink Repair Sleeve
-----------------------------	---------------------------

Body Features

Primary Product Color	Blue
-----------------------	------

Dimensions

Conductor Outside Diameter	1.5 – 2.3 mm[.059 – .09 in]
Adhesive Cut Length	21.59 mm[.85 in]
Adhesive Inside Diameter	2.13 mm[.084 in]
Sleeve Inside Diameter	3.43 mm[.135 in]
Wire Size	18 – 16 AWG
Sleeve Cut Length	19.05 mm[.75 in]

Usage Conditions

Operating Temperature Range	-65 – 150 °C
-----------------------------	--------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CJ2087-000
[HL2010E-KIT-120V](#)

Documents

Product Drawings

[D-150-C-13](#)

English

Datasheets & Catalog Pages

[1654025_Sec8_D-150_D-500_DK-621](#)

English

[Harness Repair Products Quick Reference Guide](#)

English

Product Specifications

[Side Entry Insulation Damage Repair Sleeve \(SEIDRS\)](#)

English



Installation Procedure for Series D-150-C-1X. Side Entry Insulation Damage Repair Sleeve (SEIDRS)

English