



Terminals & Splices > Splices



Sealable: **Yes**

Splice Capacity: 1

Splice Features: **Splice Kit**

Primary Product Material: **Copper**

Overall Product Length: **60 mm [2.36 in]**

Features

Product Type Features

Coaxial Cable Type	RG 393
Sealable	Yes

Configuration Features

Splice Capacity	1
Compatible With Wire & Cable Type	Coax Cable

Body Features

Insulation Sleeve Material	Fluoropolymer
Splice Features	Splice Kit
Primary Product Material	Copper

Dimensions

Overall Product Length	60 mm[2.36 in]
------------------------	----------------

Usage Conditions

Insulation Option	Fully Insulated
-------------------	-----------------

Industry Standards

Government Qualified Splice	No
-----------------------------	----

Packaging Features

Packaging Quantity	1
--------------------	---



Splices per Kit	1
Packaging Method	Kit

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUL 2021 (219) SVHC > Threshold: Pb (37% in Solder) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CJ2087-000
HL2010E-KIT-120V



Documents

Product Drawings

[D-150-Z393](#)

English

Datasheets & Catalog Pages

[1654025_Sec8_D-150_D-500_DK-621](#)

English

[Harness Repair Products Quick Reference Guide](#)

English

Product Specifications

[INSTALLATION PROCEDURE FOR CABLE SPLICE SHIELD KITS FOR RG-CABLES](#)

English