




EUROCARD

TE Internal #: 8-1393640-9
Eurocard Connectors, Receptacle, Board-to-Board, 96 Position, .1 in [2.54 mm] Centerline, Printed Circuit Board, 3 Row, Vertical, 32 Column

[View on TE.com >](#)

Connectors > PCB Connectors > Backplane Connectors > Eurocard Connectors



Connector & Housing Type: **Receptacle**
Connector System: **Board-to-Board**
Termination Post & Tail Length: **2.9 mm [.114 in]**
Number of Positions: **96**
Centerline (Pitch): **2.54 mm [.1 in]**

Features

Product Type Features

Connector & Housing Type	Receptacle
Connector System	Board-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
DIN Size	Standard
DIN Level	II

Configuration Features

Number of Positions	96
Number of Rows	3
PCB Mount Orientation	Vertical
Number of Columns	32
Number of Signal Positions	96
Rows Loaded	A, B, C

Contact Features



Contact Cross Section	.32 x .76 mm[.013 x .03 in]
Contact Type	Socket
Contact Base Material	Phosphor Bronze
Contact Current Rating (Max)	1.5 A

Termination Features

Termination Method to Printed Circuit Board	Through Hole - Solder
Termination Post & Tail Length	2.9 mm[.114 in]

Mechanical Attachment

Mating Alignment Type	Polarization
Mating Alignment	With
Panel Mount Feature	Without
PCB Mount Retention	With
PCB Mount Retention Type	Boardlock
Connector Mounting Type	Board Mount

Housing Features

Housing Material	Polyester - GF
Centerline (Pitch)	2.54 mm[.1 in]

Dimensions

Connector Height	10.6 mm
PCB Thickness (Recommended)	1.6 mm[.063 in]
Row-to-Row Spacing	2.54 mm[.1 in]

Usage Conditions

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------

Operation/Application

Shielded	No
Circuit Application	Signal

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Box
------------------	-----

Product Compliance



For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 925486-1 MOD. IV SNAP-IN HSG 96 POS.	 TE Part # 1-148057-5 096 EURO TYP C RECP 13MM ASSY	 TE Part # 5535043-5 ASSY,RECEPTACLE,EUROCARD,TYPE	 TE Part # 5535089-5 ASSEMBLY,RECEPTACLE,EUROCARD, T
 TE Part # 650473-5 096 EURO TYPE C PIN ST ASSY	 TE Part # 5536412-4 ASSY,RECEPT,EURO,TYPE C,LEAD-FREE,96,18	 TE Part # 5148057-5 ASSY,RECEPTACLE,EUROCARD,TYPE C,LEAD-FRE	 TE Part # 5650473-5 ASSY,PIN,EUROCARD,TYPE C,LEAD-



 TE Part # 650947-5 096 EURO TYPE C PIN ST ASSY	 TE Part # 5535090-4 ASSEMBLY,RECEPTACLE,EUROCARD, T	 TE Part # 3-1393641-1 V42254B2202C960=PC612 FEDERLEI	 TE Part # 5148059-5 ASSY,RECEPTACLE,EUROCARD,TYPE C,LEAD-FRE
 TE Part # 5650963-4 ASSY,RECEPTACLE,EUROCARD,TYPE	 TE Part # 9-1393644-1 V42254B1200C960=PC612 MESSERLE	 TE Part # 5650461-4 ASSY,RECEPTACLE,EUROCARD,TYPE	 TE Part # 5535043-4 ASSY,RECEPTACLE,EUROCARD,TYPE
 TE Part # 5650895-4 ASSY,RECEPT,EUROCARD,TYPE R,LE	 TE Part # 5535090-5 ASSEMBLY,RECEPTACLE,EUROCARD, T	 TE Part # 5535032-5 ASSY,RECEPTACLE,EUROCARD,TYPE C,LEAD-FRE	 TE Part # 650913-5 096 EURO TYPE C PIN BL ASSY

Documents

Product Drawings
V42254B2201C910=PC612 FEDERLEI
English

CAD Files
Customer View Model
ENG_CVM_CVM_8-1393640-9_A.2d_dxf.zip
English
3D PDF
3D
Customer View Model
ENG_CVM_CVM_8-1393640-9_A.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_8-1393640-9_A.3d_stp.zip
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications



Application Specification

English