




Heat Shrink Tubing



Primary Product Color: **Green**

Wall Type: **Single**

Expanded Inside Diameter (Min): **10.16 mm [.4 in]**

Recovered Inside Diameter (Max): **4.8 mm [.187 in]**

Shrink Ratio: **2:1**

Features

Product Type Features

Product Family	VERSAFIT
----------------	----------

Wall Type	Single
-----------	--------

Electrical Characteristics

Voltage (Max)	.6 kV
---------------	-------

Body Features

Fluid Type	Aviation Fuel, Chemicals/Solvents, De-Icing Fluid, Hydraulic Fluid, Lubricating Oil, Water
------------	--

Primary Product Color	Green
-----------------------	-------

Shrink Ratio	2:1
--------------	-----

Primary Product Material	Irradiated Modified Polyolefin
--------------------------	--------------------------------

Flexibility	Very Flexible
-------------	---------------

Dimensions

Recovered Wall Thickness (Tolerance)	.16 mm[.006 in]
--------------------------------------	-----------------



Recovered Wall Thickness (Nominal)	.64 mm[.025 in]
Expanded Inside Diameter (Min)	10.16 mm[.4 in]
Recovered Inside Diameter (Max)	4.8 mm[.187 in]
Heat Shrink Tubing Size Range	4.8 – 10.16 mm[.187 – .4 in]

Usage Conditions

Shrink Temperature (Min)	70 °C
Fluid Resistance	Splash Protection
Heat Shrink Tubing Flammability	Highly Flame-Retardant
Operating Temperature Range	-55 – 135 °C
Heat Shrink Tubing Resistance	Fluids, Strain Relief, Wrinkling
Recovery Temperature	90 °C

Product Availability

Applicable Region	Global
-------------------	--------

Packaging Features

Packaging Method	Reel
------------------	------

Other

Meets Low Outgassing Requirements	No
Product Source	Czech Republic

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CJ2087-000
HL2010E-KIT-120V



TE Part # EG1114-000
CV1981-ST-230V1600W-EU

Also in the Series | RAYCHEM Versafit



Heat Shrink Tubing(203)

Documents

Product Drawings

[VERSAFIT-3/8-5-FSP](#)

English

Datasheets & Catalog Pages

[VERSAFIT Pages from 9-1773447-9](#)

English

Product Specifications

[Quality Specification](#)

English