



Product Compliance





















[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # EP62816001 RW-175-1/4-X-76MM</p>	 <p>TE Part # NB16162001 RW-175-0.300-X-STK</p>	 <p>TE Part # NB16192001 RW-175-1/16-0-STK</p>	 <p>TE Part # NB16212001 RW-175-1/16-X-STK</p>
 <p>TE Part # NB16262001 RW-175-1/2-0-STK</p>	 <p>TE Part # NB16274001 RW-175-1/2-X-SP</p>	 <p>TE Part # NB16324001 RW-175-1/4-0-SP</p>	 <p>TE Part # NB16332001 RW-175-1/4-0-STK</p>
 <p>TE Part # NB16352001 RW-175-1/4-X-STK</p>	 <p>TE Part # NB16392001 RW-175-1/8-0-STK</p>	 <p>TE Part # NB16412001 RW-175-1/8-X-STK</p>	 <p>TE Part # NB16474001 RW-175-3/16-0-SP</p>
 <p>TE Part # NB16482001 RW-175-3/16-0-STK</p>	 <p>TE Part # NB16544001 RW-175-3/32-0-SP</p>	 <p>TE Part # NB16552001 RW-175-3/32-0-STK</p>	 <p>TE Part # NB16564001 RW-175-3/32-X-SP</p>
 <p>TE Part # NB16602001 RW-175-3/64-0-STK</p>	 <p>TE Part # NB16622001 RW-175-3/64-X-STK</p>	 <p>TE Part # NB16674001 RW-175-3/8-0-SP</p>	 <p>TE Part # NB16682001 RW-175-3/8-0-STK</p>

Also in the Series | [RAYCHEM RW-175](#)



Heat Shrink Tubing(27)

Documents

Product Drawings

[RW-175-1/16-X-SP](#)

English

Product Specifications

[Quality Specification](#)

English