



Connectors > Rectangular Connectors > Rectangular Connector Hoods & Bases



Hood & Base Connector Product Type: **Base Housing**

Hood & Base Locking Device Type: **Locking Lever**

Features

Product Type Features

Hood & Base Connector Product Type	Base Housing
------------------------------------	--------------

Body Features

Material	Nylon
Color	Gray

Mechanical Attachment

Hood & Base Locking Device Type	Locking Lever
---------------------------------	---------------

Dimensions

Length	49.8 mm[1.96 in]
Width	56.6 mm[2.228 in]
Height	37.4 mm[1.472 in]

Packaging Features

Packaging Quantity	20
Packaging Method	Box

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # T141010000-000
H10B-AG-SL



TE Part # T1410160000-000
H16B-AG-SL



TE Part # T1410240000-000
H24B-AG-SL



TE Part # T141010000-001
H10B-AG-SL, ONE RIB

Also in the Series | HDC IP65



Rectangular Connector Hoods & Bases
(1258)



Documents

Product Drawings

HB DOUBLE PLASTIC LOCKING

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_T0923004002-001_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_T0923004002-001_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_T0923004002-001_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

HEAVY DUTY CONNECTORS

English

Product Specifications

Product Specification

English

Product Specification

HB IP65 plastic locking Hood and Housing series qualification test report

English