



Connectors > PCB Connectors > PCB Connector Accessories > PCB Connector Keying



Connector Keying Accessory Type: **Keying Strip**

Operating Temperature Range: -55 – 105 °C [-67 – 221 °F]

Features

Product Type Features

Connector Keying Accessory Type	Keying Strip
---------------------------------	--------------

Body Features

Primary Product Material	Polycarbonate GF
Primary Product Color	Red

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94V-1
------------------------	----------

Packaging Features

Packaging Method	Bag
Packaging Quantity	1000

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per

homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 9-1393644-1
V42254B1200C960=PC612 MESSERLE




TE Part # 5650947-5
ASSY,PIN,EUROCARD,TYPE C,LEAD-




TE Part # 1-1393644-6
V42254B1100C960=PC612 MESSERLE




TE Part # 8-1393644-3
V42254B1200C910=PC612 MESSERLE




TE Part # 5148116-5
ASSY,PIN,EUROCARD,TYPE C,LEAD-FREE,96 PO




TE Part # 536366-5
09% EURO TYPE C PIN MFBL ASSY



TE Part # 536437-6
09% EURO TYPE C PIN MFBL ASSY



TE Part # 5536146-5
ASSY,PIN,ENH.TYPE C,EUROCARD,L-FREE,5 RO




TE Part # 650987-5
09% ENHNCD EURO PIN ASSY



TE Part # 1-536366-7
09% EURO TYPE C PIN MFBL ASSY



TE Part # 1-536437-1
09% EURO TYPE C PIN MFBL ASSY



TE Part # 1-536437-5
09% EURO TYPE C PIN MFBL ASSY



Documents

Product Drawings

KEYING BLOCK

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_926495-4_O.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_926495-4_O.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_926495-4_O.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.