



MATE-N-LOK | Universal MATE-N-LOK

TE Internal #: 926898-7

Power Contacts, Contact, 600 VAC, Gold, 20 – 14 AWG Wire Size, .5 – 2 mm<sup>2</sup> Wire Size, Wire-to-Wire, Wire & Cable, Crimp, Power, Universal MATE-N-LOK

[View on TE.com >](#)

Connectors > Power Connectors > Power Contacts



Power Contact Type: **Contact**

Operating Voltage: **600 VAC**

Contact Mating Area Plating Material: **Gold**

Wire Size: **.5 – 2 mm<sup>2</sup>**

**Features**

**Product Type Features**

Power Contact Type	Contact
Connector System	Wire-to-Wire
Connector & Contact Terminates To	Wire & Cable

**Electrical Characteristics**

Operating Voltage	600 VAC
-------------------	---------

**Contact Features**

Contact Shape & Form	Split
Contact Mating Area Plating Material	Gold
Contact Current Rating (Max)	19 A
Contact Type	Pin
Contact Retention Within Housing	With
Mating Pin Diameter	1.91 mm[.075 in]
Contact Base Material	Brass
Contact Mating Area Plating Material Thickness	.8 μm[31.49 μin]
Wire Contact Termination Area Plating Thickness	2 – 6 μm



Wire Contact Termination Area Plating Material	Tin
Wire Contact Termination Area Plating Material Finish	Matte
Contact Orientation	Straight
Contact Underplating Material	Nickel

#### Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

#### Mechanical Attachment

Contact Retention Type Within Housing	Locking Lance
Connector Mounting Type	Cable Mount (Free-Hanging)
Wire Insulation Support	Without

#### Dimensions

Wire Size	.5 – 2 mm <sup>2</sup>
Accepts Wire Insulation Diameter Range	3.3 mm[.13 in]

#### Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

#### Operation/Application

Circuit Application	Power
---------------------	-------

#### Industry Standards

CSA Rating	Certified
Glow Wire Rating	Standard Part - Not Glow Wire
VDE Tested	Yes
Agency/Standard	CSA, UL
CSA File Number	LR 7189
UL Rating	Recognized
UL File Number	E28476

#### Packaging Features

Packaging Method	Bag
Packaging Quantity	1000

#### Other

Wire/Cable Type	Discrete Wire
Wire Type	Stranded



## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts

 <p>TE Part # 539972-1 EXTRACTION TOOL</p>	 <p>TE Part # 455830-1 INSERTION TOOL</p>	 <p>TE Part # 1-480705-2 06P UNML CAP HSG RED</p>	 <p>TE Part # 1-480708-9 12P UMNL PLUG HSG BLK</p>
---	--	--	---



TE Part # 350784-1  
15P UMNL CAP HSG

TE Part # 926307-3  
6P UN-MNL AUFN-GEH

TE Part # 1-480704-2  
06P UMNL PLUG HSG RED

TE Part # 926302-1  
10& UNIV.M-N-L.PLUG

TE Part # 1-350777-2  
02P UMNL V0 PLUG HSG RED

TE Part # 350783-1  
12P UMNL CAP HSG

TE Part # 1-350778-9  
02P UMNL V0 CAP HSG BLACK

TE Part # 350735-1  
12P UMNL PLUG HSG

TE Part # 926302-3  
10P UN-MNL STECKGEH

TE Part # 926308-3  
8P UN-MNL AUFN-GEH

TE Part # 350736-1  
15P UMNL PLUG HSG

TE Part # 1-350766-2  
03P UMNL V0 PLUG HSG RED

TE Part # 1-480701-4  
03P UMNL CAP HSG YELL

TE Part # 640585-1  
06P UMNL PLUG HSG V2 NATL

TE Part # 926308-1  
8P UNIV.M-N-L.CAP

TE Part # 1-480703-9  
04P UMNL CAP HSG BLK


Also in the Series | **Universal MATE-N-LOK**

Circular Power Connectors(2)


Connector Contacts(11)

Insertion & Extraction Tools(4)

Power Contacts(207)



Rectangular Boots &amp; Strain Relief(35)



Rectangular Connector Adapters(7)



Rectangular Connector Hardware(1)



Rectangular Connector Housings(2)



Rectangular Connector Keying Plugs(3)



Rectangular Connector Locking(4)



Rectangular Connector Seals(26)



Rectangular Power Connectors(728)

## Documents

### Product Drawings

#### UNIV MNL SPLIT PIN LP

English

### CAD Files

#### Customer View Model

[ENG\\_CVM\\_926898-7\\_P1.3d\\_igs.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_926898-7\\_P1.3d\\_stp.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_926898-7\\_P1.2d\\_dxf.zip](#)

English

### 3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.