

T1419320000-000 ✓ ACTIVE

HDC | HDC IP65

TE Internal #: T1419320000-000

TE Internal Description: H32A-AG

[View on TE.com >](#)



Connectors > Rectangular Connectors > Rectangular Connector Hoods & Bases



Hood & Base Connector Product Type: **Base Housing**

Cable Entry Location: **Bottom**

Hood & Base Locking Device Type: **Locking**

Sealable: **Yes**

Circuit Application: **Power & Signal**

Features

Product Type Features

Product Size	7
Hood & Base Connector Product Type	Base Housing
Sealable	Yes

Body Features

Material	Die Cast Aluminum
Cable Entry Location	Bottom

Mechanical Attachment

Locking Device Location	Housing
Hood & Base Locking Device Type	Locking

Dimensions

Length	102 mm
--------	--------

Usage Conditions

Corrosion Protected	Yes
---------------------	-----

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Packaging Features

Packaging Method	Box
------------------	-----



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # T1209320232-000 H32A-TS/G-2M32</p>	 <p>TE Part # T1319320120-000 H32A-TS-M20</p>	 <p>TE Part # T1319320125-000 H32A-TS-M25</p>	 <p>TE Part # T1319320132-000 H32A-TS-M32</p>
-----------------------------------------------------------------------------------------------------------------------------------------	--------------------------------------------------------------------------------------------------------------------------------------	----------------------------------------------------------------------------------------------------------------------------------------	----------------------------------------------------------------------------------------------------------------------------------------



TE Part # T1319320140-000
H32A-TS-M40



TE Part # T1329320121-000
H32A-TG-PG21



TE Part # T1329320125-000
H32A-TG-M25



TE Part # T1329320129-000
H32A-TG-PG29



TE Part # T1329320132-000
H32A-TG-M32



TE Part # T1329320140-000
H32A-TG-M40



TE Part # T1329320150-000
H32A-TG-M50



TE Part # T2010322201-000
HA-016-F 17-32



TE Part # T1319320121-000
H32A-TS-PG21



TE Part # T2010324201-000
HA-016-FC 17-32



TE Part # T1319320116-000
H32A-TS-PG16



TE Part # T2010322201-001
HA-016-F 17-32



TE Part # T2020502201-000
HD-025-F 26-50

Also in the Series | **HDC IP65**



Rectangular Connector Hoods & Bases
(1258)

Documents



Product Drawings

[H32A-AG](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_T1419320000-000_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_T1419320000-000_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_T1419320000-000_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Heavy Duty Connectors](#)

English

[HEAVY DUTY CONNECTORS](#)

English

Product Specifications

[Application Specification](#)

English

[Application Specification](#)