



Connectors > Rectangular Connectors > Rectangular Connector Hoods & Bases



Hood & Base Connector Product Type: **Base Housing**

Cable Entry Location: **Bottom**

Hood & Base Locking Device Type: **Screwlock**

## Features

### Product Type Features

Product Size	3
Hood & Base Connector Product Type	Base Housing

### Body Features

Material	Die Cast Aluminum
Color	Black
Cable Entry Location	Bottom

### Mechanical Attachment

Locking Device Location	Hood
Hood & Base Locking Device Type	Screwlock

### Dimensions

Length	96 mm[3.78 in]
Width	56 mm[2.205 in]
Height	21.9 mm[.862 in]

### Usage Conditions

Corrosion Protected	Yes
---------------------	-----

### Packaging Features



Packaging Quantity	1
Packaging Method	Bag

### Product Compliance


[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not reviewed for solder process capability

#### Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts

 <p>TE Part # T1912060116-009 H6BPR-TSHC-PG16-EMC-C</p>	 <p>TE Part # T1912060120-009 H6BPR-TSHC-M20-EMC-C</p>	 <p>TE Part # T1912060121-009 H6BPR-TSHC-PG21-EMC-C</p>	 <p>TE Part # T1912060125-009 H6BPR-TSHC-M25-EMC-C</p>
--	---	--	---



## Also in the Series | HDC IP68 EMC



## Documents

### Product Drawings H6BPR-AGC-EMC-C

English

### CAD Files

3D PDF

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_T1932060000-009\\_A.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_T1932060000-009\\_A.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_T1932060000-009\\_A.3d\\_stp.zip](#)

English



By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

## Datasheets & Catalog Pages

### HEAVY DUTY CONNECTORS

English

---

## Product Specifications

### Application Specification

English

### Application Specification

---

## Product Environmental Compliance

### Product Compliance

English

### Product Compliance

English