

T2010322101-000 ✓ ACTIVE

HDC | HDC HA

TE Internal #: T2010322101-000

Rectangular Contact Inserts, Pin, 16+PE, Screw Terminal, 16 Position, 14 – 20 AWG Wire Size, .5 – 2.5 mm² Wire Size, 10 A, Power & Signal, HDC HA

[View on TE.com >](#)



Connectors > Rectangular Connectors > Rectangular Contact Inserts



Contact Type: **Pin**

Contact Insert Pole Configuration: **16+PE**

Termination Method to Wire & Cable: **Screw Terminal**

Number of Positions: **16**

Sealable: **No**

Features

Product Type Features

Product Type	Contact Insert
Sealable	No

Configuration Features

Number of Positions	16
---------------------	----

Contact Features

Contact Type	Pin
Contact Insert Pole Configuration	16+PE
Contact Current Rating (Max)	10 A

Termination Features

Termination Method to Wire & Cable	Screw Terminal
------------------------------------	----------------

Dimensions

Wire Size	.5 – 2.5 mm ²
-----------	--------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU

Compliant with Exemptions

EU ELV Directive 2000/53/EC

Compliant with Exemptions

China RoHS 2 Directive MIIT Order No 32, 2016

Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2022
(224)Candidate List Declared Against: JAN 2022
(223)

SVHC > Threshold:

Pb (3.7% in Pb-Alloy in Copper)

Article Safe Usage Statements:

Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Not Low Halogen - contains Br or Cl > 900 ppm.

Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # T1209320232-000
H32A-TS/G-2M32TE Part # T1319320120-000
H32A-TS-M20TE Part # T1319320140-000
H32A-TS-M40TE Part # T1329320121-000
H32A-TG-PG21TE Part # T1329320125-000
H32A-TG-M25TE Part # T1329320129-000
H32A-TG-PG29TE Part # T1329320132-000
H32A-TG-M32TE Part # T1329320140-000
H32A-TG-M40



Also in the Series | HDC HA



Documents

Product Drawings

[HA-016-M 17-32](#)

English

CAD Files

[3D PDF](#)

[3D](#)

Customer View Model

[ENG_CVM_CVM_T2010322101-000_B.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_T2010322101-000_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_T2010322101-000_B.3d_stp.zip](#)

English



By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Heavy Duty Connectors

English

HEAVY DUTY CONNECTORS

English

Product Specifications

Application Specification

English

Agency Approvals

Agency Approval Document

English