



HDC | HDC HD

TE Internal #: T2031082101-007

Rectangular Contact Inserts, Pin, Pin, 108, Crimp Terminal, 108 Position, Wire & Cable, 26 – 14 AWG Wire Size, 10 A, Power & Signal, HDC HD

[View on TE.com >](#)

Connectors > Rectangular Connectors > Rectangular Contact Inserts > HDC HD HDD Insert Series, Rail Compliant



Rectangular Connector Insert Type: **Pin**

Contact Type: **Pin**

Contact Insert Pole Configuration: **108**

Termination Method to Wire & Cable: **Crimp Terminal**

Number of Positions: **108**

[All HDC HD HDD Insert Series, Rail Compliant \(4\)](#)

## Features

### Product Type Features

Product Type	Insert
Product Size	8
Rectangular Connector Insert Type	Pin
Connector & Contact Terminates To	Wire & Cable

### Configuration Features

Number of Positions	108
---------------------	-----

### Electrical Characteristics

Power Circuit Voltage	250 V
Power Circuit Current	10 A
Current Rating	10 A

### Body Features

Color	Gray
-------	------

### Contact Features

Contact Type	Pin
Contact Insert Pole Configuration	108



Contact Current Rating (Max)	10 A
------------------------------	------

### Termination Features

Termination Method to Wire & Cable	Crimp Terminal
------------------------------------	----------------

### Dimensions

Wire Size	26 – 14 AWG
-----------	-------------

### Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

### Packaging Features

Packaging Method	Box
------------------	-----

Packaging Quantity	5
--------------------	---

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability




#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts



## Also in the Series | HDC HD



## Documents

### Product Drawings

[HDD-108-M](#)

English

### CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_T2031082101-007\\_A.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_T2031082101-007\\_A.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_T2031082101-007\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

[EN45545 COMPLIANT HDC INSERTS](#)

English

### Product Specifications

[Application Specification](#)

English

