




Connectors > RF Coax Connectors > Coax Terminators



Compatible With RF Cable Type: **RG 174, RG 316**
Connector & Contact Terminates To: **Wire & Cable**
Circuit Application: **Signal**

Features

Product Type Features

Compatible With RF Cable Type	RG 174, RG 316
Connector & Contact Terminates To	Wire & Cable

Body Features

Body Plating Material	Tin
Body Material	Brass

Contact Features

RF Connector Center Contact Plating Material	Tin
Crimp Type	Braid Termination
RF Connector Center Contact Material	Brass

Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Packaging Features

Packaging Method	Loose Piece
------------------	-------------

Other

--	--

RF Connector Comment

Loose form parts with preformed tabs.

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU

Compliant

EU ELV Directive 2000/53/EC

Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2022 (224)
 Candidate List Declared Against: JUNE 2022 (224)
 Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Documents

[Product Drawings](#)

[BRAID PIC TERMINAL, LF PLTG](#)



English

CAD Files

Customer View Model

[ENG_CVM_9-226176-2_N.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_9-226176-2_N.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_9-226176-2_N.2d_dxf.zip](#)

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Environmental Compliance

Product Compliance

English

Product Compliance

English

Instruction Sheets

Instruction Sheet (U.S.)

English

AMP* BRAID-PIC TERMINALS FOR PRINTED CIRCUIT BOARD APPLICATIONS

English