



T2K

TE Internal #: A23615-000

Standard Labels, UL Listed, Label Width 22.9 mm [.9 in], Label Height .25 in [6.4 mm], White, Polyimide, Label Thickness 118 Micron, T2K

[View on TE.com >](#)

Identification & Labeling > Labels > Standard Labels > T2K WHITE POLYIMIDE LABELS



Label Type: **PCB Identification**

Label Style: **Die-Cut**

Label Adhesive Type: **High Temperature Permanent Acrylic Adhesive**

UL Listed: **Yes**

Label Width: **22.9 mm [.9 in]**

[All T2K WHITE POLYIMIDE LABELS \(15\)](#)

## Features

### Product Type Features

Label Type	PCB Identification
------------	--------------------

### Body Features

Label Color	White
-------------	-------

### Usage Conditions

Operating Temperature Range	-40 – 300 °C[-40 – 572 °F]
-----------------------------	----------------------------

### Printer/Label Features

Number of Labels Across	3
Recommended Printer Ribbon	See Printer Ribbon Matrix
Label Style	Die-Cut
Label Width	22.9 mm[.9 in]
Label Height	6.4 mm[.25 in]
Label Material	Polyimide
Label Thickness	118 Micron

### Industry Standards

UL Listed	Yes
-----------	-----



### Packaging Features

Packaging Quantity	10000
Packaging Method	Roll

### Other

Label Adhesive Type	High Temperature Permanent Acrylic Adhesive
---------------------	---

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not lead free process capable

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts



## Also in the Series | T2K



### Documents

#### Product Drawings

T2K-229064-10-9

English

#### Datasheets & Catalog Pages

IDENTIFICATION SELECTION GUIDE

English

#### T2K labels

English

#### Product Specifications

IDENTIFICATION PRINTER PRODUCT RIBBON MATRIX

English