



Connectors > Rectangular Connectors > Rectangular Contact Inserts



Rectangular Connector Insert Type: **HE**
Contact Type: **Socket**
Contact Insert Pole Configuration: **24**
Termination Method to Wire & Cable: **Crimp Terminal**
Number of Positions: **24**

Features

Product Type Features

Product Type	Insert
Rectangular Connector Insert Type	HE
Sealable	No

Configuration Features

Number of Positions	24
---------------------	----

Contact Features

Contact Type	Socket
Contact Insert Pole Configuration	24

Termination Features

Termination Method to Wire & Cable	Crimp Terminal
------------------------------------	----------------

Dimensions

Wire Size	.14 – 4 mm²
-----------	-------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # T1500482000-000
H48B-AG-LB

TE Part # T2030002040-000
CEF-4.0

TE Part # T2040484101-000
HE-024-MC 25-48

Also in the Series | HDC HE

Connector Contacts(32)

Rectangular Contact Inserts(127)



Documents

Product Drawings

HE-024-FC 25-48

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_T2040484201-000_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_T2040484201-000_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_T2040484201-000_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Heavy Duty Connectors

English

HEAVY DUTY CONNECTORS

English

Product Specifications

Application Specification

English

Application Specification

Agency Approvals

Agency Approval Document

English