

VERSAFLEX-03-0-SP ✓ ACTIVE

RAYCHEM | RAYCHEM VERSAFLEX


TE Internal #: C145614001

Heat Shrink Tubing, Black, Braid Wall, Polyester, Non-Flame-Retardant, Box, -50 – 150 °C, Resistant To Mechanical Damage, Flexible, RAYCHEM VERSAFLEX

[View on TE.com >](#)



Heat Shrink Tubing



Primary Product Color: **Black**

Wall Type: **Braid**

Primary Product Material: **Polyester**

Heat Shrink Tubing Flammability: **Non-Flame-Retardant**

Packaging Method: **Box**

Features

Product Type Features

| | |
|----------------|-----------|
| Product Family | VERSAFLEX |
| Wall Type | Braid |

Body Features

| | |
|--------------------------|-----------|
| Primary Product Color | Black |
| Primary Product Material | Polyester |
| Flexibility | Flexible |

Dimensions

| | |
|-------------------------------|---------------------------|
| Heat Shrink Tubing Size Range | 1 – 5 mm [.039 – .196 in] |
|-------------------------------|---------------------------|

Usage Conditions

| | |
|---------------------------------|---------------------|
| Fluid Resistance | Splash Protection |
| Heat Shrink Tubing Flammability | Non-Flame-Retardant |
| Operating Temperature Range | -50 – 150 °C |
| Heat Shrink Tubing Resistance | Mechanical Damage |

Product Availability

| | |
|-------------------|--------|
| Applicable Region | Global |
|-------------------|--------|

Packaging Features

| | |
|------------------|-----|
| Packaging Method | Box |
|------------------|-----|



Other

| | |
|-----------------------------------|--------|
| Meets Low Outgassing Requirements | No |
| Product Source | Europe |

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

| | |
|---|--|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC |
| Halogen Content | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Not applicable for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # CJ2087-000
HL2010E-KIT-120V



TE Part # EG1114-000
CV1981-ST-230V1600W-EU

Also in the Series | **RAYCHEM VERSAFLEX**



Heat Shrink Tubing(30)

Documents

Datasheets & Catalog Pages

[VERSAFLEX - Expandable Braided Polyester Sleeving](#)

English

Product Specifications

[Quality Specification](#)

English