




Terminals & Splices > Splices



Wire Size: .95 – 3.37 mm<sup>2</sup>

Sealable: **Yes**

Splice Features: **Splice Kit**

Barrel Inside Diameter: **2.54 mm [ .1 in ]**

## Features

### Product Type Features

Splice Accessory Type	Splice
Sealable	Yes
Serrated	No
Wire Insulation Support Retention Type	Non-Insulation Support

### Configuration Features

Splice Configuration	Single to Single
Number of Serrations	0
Compatible With Wire & Cable Type	Discrete Wire

### Body Features

Insulation Sleeve Material	Fluoropolymer
Weight per Piece	.16 g
Plating Material	Nickel
Insulation Material	Heat Shrink Radiation-Crosslinked Modified Fluoropolymer
Splice Features	Splice Kit
Primary Product Material	Copper Alloy

### Contact Features

Barrel Type	Closed
-------------	--------

### Termination Features



Termination Method	Crimp
--------------------	-------

### Dimensions

Wire Size	2426 – 5874 CMA
Barrel Inside Diameter	2.54 mm[.1 in]
Overall Product Length	29.21 mm[1.15 in]

### Usage Conditions

Insulation Option	Fully Insulated
Operating Temperature Range	-55 – 200 °C[-67 – 392 °F]

### Operation/Application

Heavy Duty	No
------------	----

### Industry Standards

Government Qualified Splice	Yes
-----------------------------	-----

### Packaging Features

Packaging Quantity	100
Packaging Method	Bag/Box

### Other

Barrel Color	Clear
Comment	Parts will meet all performance requirements of SAE AS-81824 when properly installed.

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts





## Documents

### Product Drawings

[D-200-84](#)

English

### Datasheets & Catalog Pages

[1654025\\_Sec8\\_D-200](#)

English

[RAYCHEM\\_D-200\\_MINISEAL\\_CRIMP\\_SPLICES](#)

English