


STV08 Product Details

Have a Question?

Chat with a Product Information Specialist



STV08

TE Internal Number: 1977104 - 4

[Active](#)

DIP & SIP Switches - Standard

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- ? Switch
- ? Switch Type = SIP
- ? PCB Mount Style = Through Hole
- ? Actuator Style = Slide
- ? Not Sealed

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- ? [SIP SWITCH \(STV02 - 10 SERIES \)](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? [SWITCHES CORE PROGRAM CATALOG](#) (PDF, English)

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files:

- ? None Available

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? Product Type = Switch
- ? PCB Mount Style = Through Hole
- ? [Actuator Style](#) = Slide
- ? Sealed = No
- ? [Number of Switches](#) = 8
- ? Mount Angle = Vertical

Termination Related Features:

- ? Termination Post Length (mm [in]) = 3.60 [0.142]

Body Related Features:

- ? Switch Type = SIP
- ? Series = S
- ? Centerline (mm [in]) = 2.54 [0.100]
- ? Height (mm [in]) = 6.22 [0.244]
- ? Length (mm [in]) = 23.52 [0.926]
- ? Actuator Color = White

Contact Related Features:

- ? Auto - Insertable = No
- ? Contact Base Material = Copper Alloy
- ? Contact Plating, Mating Area, Material = Gold Flash

Housing Related Features:

- ? Low Profile = No
- ? Housing Color = Black
- ? Housing Material = PPS
- ? UL Flammability Rating = UL 94V - 0

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Other:

- ? Brand = Alcoswitch

Corporate Information

- [Who We Are](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)

Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat with Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage Your Account](#)

Sign up for our eNewsletter

Enter your email address

Follow Us On:



Visit Us On:

