



Have a Question?

What can we

[Chat with a Product Information Specialist](#)


Share



Print



Email

1825161-1 Product Details



1825161-1

TE Internal Number: 1825161-1

 [Active](#)

Slide Switches


[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- 3 Positions
- Single Pole - Three Throw Configuration (Pole-Throw)
- Actuator Style = Top
- Actuator Color = Black
- STS Series

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

[Add to My Part List](#)
[Request Sample](#)
[Find Similar Products](#)
[Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [SLIDE SWITCH, STS1300PC & STS1400PC SERIES](#) (PDF, English)

Catalog Pages/Data Sheets:

- [SWITCHES CORE PROGRAM CATALOG](#) (PDF, English)

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Configuration (Pole-Throw) = Single Pole - Three Throw
- Actuator Style = Top
- Mount Angle = Vertical
- Terminal Configuration = Standard
- Grade = Economy
- Termination Type = PC

Electrical Characteristics:

- Contact Rating = 250mA @ 125 VAC

Body Related Features:

- [Number of Positions](#) = 3
- Actuator Color = Black
- Series = STS
- Mount Style = Through-Hole
- Switch Style = Low Profile
- PCB Tail Length (mm [in]) = 2.50 [0.098]
- Actuator Material = POM
- Actuator Travel = 2.50 [.098]

Contact Related Features:

- Contact Plating = Silver

Housing Related Features:

- UL Flammability Rating = UL 94-HB

Configuration Related Features:

- Number of Actuators = Single

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Identification Marking:

- Stamped Marking = With

Other:

- Brand = Alcoswitch