

Section 1. Identification

GHS product identifier : FT 100
Product code : 53-G 182(400mL)
SDS no. : L -172E
Product type : Aerosol

Relevant identified uses of the substance or mixture and uses advised against

Identified uses : Foaming stainless steel and glass surface cleaner.

Manufacturer : Walter Surface Technologies Inc.
 5977 Trans Canada Highway
 Pointe-Claire, QC H9R 1C1
 Canada
 info@walter.com
 www.walter.com
 General Information: 1-888-592-5837

Emergency telephone number (with hours of operation) : INFOTRAC® 1-800-535-5053. International call collect: 1-352-323-3500
 24 hours/day, 7 days/week.

Section 2. Hazards identification

OSHA/HCS status : This material is considered hazardous by the OSHA Hazard Communication Standard (29 CFR 1910.1200).

Classification of the substance or mixture : FLAMMABLE AEROSOLS - Category 1
 GASES UNDER PRESSURE - Compressed gas
 SERIOUS EYE DAMAGE/ EYE IRRITATION - Category 2A

GHS label elements

Hazard pictograms :



Signal word : Danger

Hazard statements : H222 - Extremely flammable aerosol.
 H280 - Contains gas under pressure; may explode if heated.
 H319 - Causes serious eye irritation.

Precautionary statements

Prevention : P280 - Wear eye or face protection.
 P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
 P211 - Do not spray on an open flame or other ignition source.
 P264 - Wash hands thoroughly after handling.
 P251 - Pressurized container: Do not pierce or burn, even after use.

Response : P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
 P337 + P313 - If eye irritation persists: Get medical attention.

Section 2. Hazards identification

Storage : P410 - Protect from sunlight.
P412 - Do not expose to temperatures exceeding 50°C/122°F.
P403 - Store in a well-ventilated place.

Disposal : Not applicable.

Hazards not otherwise classified : None known.

Section 3. Composition/information on ingredients

Substance/mixture : Mixture
Product code : 53-G 182(400mL)

Ingredient name	%	CAS number
Isopropyl Alcohol	≥10 - <20	67-63-0
Ammonia	<0.25	1336-21-6

The exact percentage (concentration) in the composition has been withheld as a trade secret in accordance with paragraph (i) of §1910.1200.

There are no additional ingredients present which, within the current knowledge of the supplier and in the concentrations applicable, are classified as hazardous to health or the environment and hence require reporting in this section.

Occupational exposure limits, if available, are listed in Section 8.

Section 4. First aid measures

Description of necessary first aid measures

- Eye contact** : Immediately flush eyes with plenty of water, occasionally lifting the upper and lower eyelids. Check for and remove any contact lenses. Continue to rinse for at least 20 minutes. Get medical attention.
- Inhalation** : Remove victim to fresh air and keep at rest in a position comfortable for breathing. If not breathing, if breathing is irregular or if respiratory arrest occurs, provide artificial respiration or oxygen by trained personnel. It may be dangerous to the person providing aid to give mouth-to-mouth resuscitation. Get medical attention if adverse health effects persist or are severe. If unconscious, place in recovery position and get medical attention immediately. Maintain an open airway. Loosen tight clothing such as a collar, tie, belt or waistband.
- Skin contact** : Flush contaminated skin with plenty of water. Get medical attention if symptoms occur. Wash clothing before reuse. Clean shoes thoroughly before reuse.
- Ingestion** : Wash out mouth with water. Remove dentures if any. Remove victim to fresh air and keep at rest in a position comfortable for breathing. If material has been swallowed and the exposed person is conscious, give small quantities of water to drink. Stop if the exposed person feels sick as vomiting may be dangerous. Do not induce vomiting unless directed to do so by medical personnel. If vomiting occurs, the head should be kept low so that vomit does not enter the lungs. Get medical attention if adverse health effects persist or are severe. Never give anything by mouth to an unconscious person. If unconscious, place in recovery position and get medical attention immediately. Maintain an open airway. Loosen tight clothing such as a collar, tie, belt or waistband.

Most important symptoms/effects, acute and delayed

Potential acute health effects

- Eye contact** : Causes serious eye irritation.
- Inhalation** : No known significant effects or critical hazards.
- Skin contact** : No known significant effects or critical hazards.

Section 4. First aid measures

Ingestion : No known significant effects or critical hazards.

Over-exposure signs/symptoms

Eye contact : Adverse symptoms may include the following:
pain or irritation
watering
redness

Inhalation : Adverse symptoms may include the following:
respiratory tract irritation
coughing

Skin contact : No known significant effects or critical hazards.

Ingestion : No known significant effects or critical hazards.

Indication of immediate medical attention and special treatment needed, if necessary

Notes to physician : Treat symptomatically. Contact poison treatment specialist immediately if large quantities have been ingested or inhaled.

Specific treatments : No specific treatment.

Protection of first-aiders : No action shall be taken involving any personal risk or without suitable training. It may be dangerous to the person providing aid to give mouth-to-mouth resuscitation.

See toxicological information (Section 11)

Section 5. Fire-fighting measures

Extinguishing media

Suitable extinguishing media : In case of fire, use foam, dry chemical or carbon dioxide.

Unsuitable extinguishing media : Do not use water jet.

Specific hazards arising from the chemical : Extremely flammable aerosol. Runoff to sewer may create fire or explosion hazard. In a fire or if heated, a pressure increase will occur and the container may burst, with the risk of a subsequent explosion. Gas may accumulate in low or confined areas or travel a considerable distance to a source of ignition and flash back, causing fire or explosion. Bursting aerosol containers may be propelled from a fire at high speed.

Hazardous thermal decomposition products : Decomposition products may include the following materials:
carbon dioxide
carbon monoxide

Special protective actions for fire-fighters : Promptly isolate the scene by removing all persons from the vicinity of the incident if there is a fire. No action shall be taken involving any personal risk or without suitable training. Move containers from fire area if this can be done without risk. Use water spray to keep fire-exposed containers cool.

Special protective equipment for fire-fighters : Fire-fighters should wear appropriate protective equipment and self-contained breathing apparatus (SCBA) with a full face-piece operated in positive pressure mode.

Section 6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

- For non-emergency personnel** : No action shall be taken involving any personal risk or without suitable training. Evacuate surrounding areas. Keep unnecessary and unprotected personnel from entering. In the case of aerosols being ruptured, care should be taken due to the rapid escape of the pressurized contents and propellant. If a large number of containers are ruptured, treat as a bulk material spillage according to the instructions in the clean-up section. Do not touch or walk through spilled material. Shut off all ignition sources. No flares, smoking or flames in hazard area. Avoid breathing vapor or mist. Provide adequate ventilation. Wear appropriate respirator when ventilation is inadequate. Put on appropriate personal protective equipment.
- For emergency responders** : If specialized clothing is required to deal with the spillage, take note of any information in Section 8 on suitable and unsuitable materials. See also the information in "For non-emergency personnel".

- Environmental precautions** : Avoid dispersal of spilled material and runoff and contact with soil, waterways, drains and sewers. Inform the relevant authorities if the product has caused environmental pollution (sewers, waterways, soil or air).

Methods and materials for containment and cleaning up

- Spill** : Stop leak if without risk. Move containers from spill area. Use spark-proof tools and explosion-proof equipment. Approach release from upwind. Prevent entry into sewers, water courses, basements or confined areas. Wash spillages into an effluent treatment plant or proceed as follows. Contain and collect spillage with non-combustible, absorbent material e.g. sand, earth, vermiculite or diatomaceous earth and place in container for disposal according to local regulations (see Section 13). Dispose of via a licensed waste disposal contractor. Contaminated absorbent material may pose the same hazard as the spilled product. Note: see Section 1 for emergency contact information and Section 13 for waste disposal.

Section 7. Handling and storage

Precautions for safe handling

- Protective measures** : Put on appropriate personal protective equipment (see Section 8). Pressurized container: protect from sunlight and do not expose to temperatures exceeding 50°C. Do not pierce or burn, even after use. Do not ingest. Avoid contact with eyes, skin and clothing. Avoid breathing gas. Avoid breathing vapor or mist. Use only with adequate ventilation. Wear appropriate respirator when ventilation is inadequate. Store and use away from heat, sparks, open flame or any other ignition source. Use explosion-proof electrical (ventilating, lighting and material handling) equipment. Use only non-sparking tools. Empty containers retain product residue and can be hazardous.
- Advice on general occupational hygiene** : Eating, drinking and smoking should be prohibited in areas where this material is handled, stored and processed. Workers should wash hands and face before eating, drinking and smoking. See also Section 8 for additional information on hygiene measures.
- Conditions for safe storage, including any incompatibilities** : Store in accordance with local regulations. Store away from direct sunlight in a dry, cool and well-ventilated area, away from incompatible materials (see Section 10) and food and drink. Protect from sunlight. Eliminate all ignition sources. Use appropriate containment to avoid environmental contamination.

Section 8. Exposure controls/personal protection

Control parameters

Occupational exposure limits

Ingredient name	Exposure limits
Isopropyl Alcohol	ACGIH TLV (United States, 3/2017). TWA: 200 ppm 8 hours. STEL: 400 ppm 15 minutes. NIOSH REL (United States, 10/2016). TWA: 400 ppm 10 hours. TWA: 980 mg/m ³ 10 hours. STEL: 500 ppm 15 minutes. STEL: 1225 mg/m ³ 15 minutes. OSHA PEL (United States, 6/2016). TWA: 400 ppm 8 hours. TWA: 980 mg/m ³ 8 hours.
Ammonia	None.

- Appropriate engineering controls** : No personal respiratory protective equipment normally required. Avoid breathing dust/fume/gas/mist/vapors/spray. When workers are facing concentrations above the exposure limit they must use appropriate certified respirators.
- Environmental exposure controls** : Emissions from ventilation or work process equipment should be checked to ensure they comply with the requirements of environmental protection legislation.

Individual protection measures

- Hygiene measures** : Wash hands, forearms and face thoroughly after handling chemical products, before eating, smoking and using the lavatory and at the end of the working period. Appropriate techniques should be used to remove potentially contaminated clothing.
- Eye/face protection** : Safety eyewear complying with an approved standard should be used when a risk assessment indicates this is necessary to avoid exposure to liquid splashes, mists, gases or dusts. If contact is possible, the following protection should be worn, unless the assessment indicates a higher degree of protection: chemical splash goggles.
- Skin protection**
 - Hand protection** : Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary. Considering the parameters specified by the glove manufacturer, check during use that the gloves are still retaining their protective properties. It should be noted that the time to breakthrough for any glove material may be different for different glove manufacturers. In the case of mixtures, consisting of several substances, the protection time of the gloves cannot be accurately estimated. Recommended: Nitrile gloves. (Permeation time > 8 hours)
 - Body protection** : Personal protective equipment for the body should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product. When there is a risk of ignition from static electricity, wear anti-static protective clothing. For the greatest protection from static discharges, clothing should include anti-static overalls, boots and gloves.
 - Other skin protection** : Appropriate footwear and any additional skin protection measures should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.
- Respiratory protection** : Use a NIOSH/MSHA approved respirator if there is a risk of exposure at levels exceeding the exposure limits. Advice should be sought from respiratory protection specialists.

Section 9. Physical and chemical properties

Appearance

Physical state	: Liquid. [Aerosol.]
Color	: Colorless.
Odor	: Characteristic.
Odor threshold	: Not available.
pH	: 9.5
Melting point	: Not available.
Boiling point	: Not applicable.
Flash point	: -60°C (-76°F)
Evaporation rate	: Not applicable.
Flammability (solid, gas)	: Not available.
Lower and upper explosive (flammable) limits	: Lower: 2% Upper: 12%
Vapor pressure	: 400 kPa (3000.2 mm Hg) [room temperature]
Vapor density	: Not available.
Relative density	: 0.9 g/ml @ 20°C (68°F)
Solubility	: Not available.
Partition coefficient: n-octanol/water	: Not available.
Auto-ignition temperature	: 365°C (689°F)
Decomposition temperature	: Not available.
Viscosity	: Not available.
Flow time (ISO 2431)	: Not available.
VOC content	: 24.4 % (w/w)

Aerosol product

Type of aerosol	: Spray
Heat of combustion	: 4.84 kJ/g

Section 10. Stability and reactivity

Reactivity	: No specific test data related to reactivity available for this product or its ingredients.
Chemical stability	: The product is stable.
Possibility of hazardous reactions	: Under normal conditions of storage and use, hazardous reactions will not occur.
Conditions to avoid	: Avoid all possible sources of ignition (spark or flame).
Incompatible materials	: Reactive or incompatible with the following materials: oxidizing materials.
Hazardous decomposition products	: Under normal conditions of storage and use, hazardous decomposition products should not be produced.

Section 11. Toxicological information

Information on toxicological effects

Acute toxicity

Product/ingredient name	Result	Species	Dose	Exposure
Isopropyl Alcohol	LD50 Dermal	Rabbit	12800 mg/kg	-
	LD50 Oral	Rat	5000 mg/kg	-
Ammonia	LD50 Oral	Rat	350 mg/kg	-

Irritation/Corrosion

Product/ingredient name	Result	Species	Score	Exposure	Observation
Isopropyl Alcohol	Eyes - Moderate irritant	Rabbit	-	24 hours 100 mg	-
	Eyes - Moderate irritant	Rabbit	-	10 mg	-
	Eyes - Severe irritant	Rabbit	-	100 mg	-
	Skin - Mild irritant	Rabbit	-	500 mg	-
Ammonia	Eyes - Severe irritant	Rabbit	-	250 µg	-
	Eyes - Severe irritant	Rabbit	-	0.5 minutes 1 mg	-

Sensitization

There is no data available.

Mutagenicity

There is no data available.

Carcinogenicity

Classification

Product/ingredient name	OSHA	IARC	NTP
Isopropyl Alcohol	-	3	-

Reproductive toxicity

There is no data available.

Teratogenicity

There is no data available.

Specific target organ toxicity (single exposure)

Name	Category	Target organs
Isopropyl Alcohol	Category 3	Narcotic effects
Ammonia	Category 3	Respiratory tract irritation

Specific target organ toxicity (repeated exposure)

There is no data available.

Aspiration hazard

There is no data available.

Information on the likely routes of exposure : Dermal contact. Eye contact. Inhalation. Ingestion.

Potential acute health effects

- Eye contact** : Causes serious eye irritation.
- Inhalation** : No known significant effects or critical hazards.
- Skin contact** : No known significant effects or critical hazards.
- Ingestion** : No known significant effects or critical hazards.

Symptoms related to the physical, chemical and toxicological characteristics

Section 11. Toxicological information

- Eye contact** : Adverse symptoms may include the following:
 pain or irritation
 watering
 redness
- Inhalation** : Adverse symptoms may include the following:
 respiratory tract irritation
 coughing
- Skin contact** : No known significant effects or critical hazards.
- Ingestion** : No known significant effects or critical hazards.

Delayed and immediate effects and also chronic effects from short and long term exposure

Short term exposure

- Potential immediate effects** : No known significant effects or critical hazards.
- Potential delayed effects** : No known significant effects or critical hazards.

Long term exposure

- Potential immediate effects** : No known significant effects or critical hazards.
- Potential delayed effects** : No known significant effects or critical hazards.

Potential chronic health effects

- General** : No known significant effects or critical hazards.
- Carcinogenicity** : No known significant effects or critical hazards.
- Mutagenicity** : No known significant effects or critical hazards.
- Teratogenicity** : No known significant effects or critical hazards.
- Developmental effects** : No known significant effects or critical hazards.
- Fertility effects** : No known significant effects or critical hazards.

Numerical measures of toxicity

Acute toxicity estimates

Route	ATE value
Oral	37037 mg/kg

Section 12. Ecological information

Toxicity

Product/ingredient name	Result	Species	Exposure
Isopropyl Alcohol	Acute EC50 10100 mg/L Fresh water Acute LC50 1400000 µg/L Marine water	Daphnia - Daphnia magna Crustaceans - Crangon crangon	48 hours 48 hours
Ammonia	Acute LC50 4200 mg/L Fresh water Acute LC50 37 ppm Fresh water	Fish - Rasbora heteromorpha Fish - Gambusia affinis - Adult	96 hours 96 hours

Persistence and degradability

There is no data available.

Bioaccumulative potential

Section 12. Ecological information

Product/ingredient name	LogP _{ow}	BCF	Potential
Isopropyl Alcohol	0.05	-	low

Mobility in soil

Soil/water partition coefficient (K_{oc}) : Not available.

Other adverse effects : No known significant effects or critical hazards.

Section 13. Disposal considerations

Disposal methods : The generation of waste should be avoided or minimized wherever possible. Disposal of this product, solutions and any by-products should comply with the requirements of environmental protection and waste disposal legislation and any regional local authority requirements. Dispose of surplus and non-recyclable products via a licensed waste disposal contractor. Waste should not be disposed of untreated to the sewer unless fully compliant with the requirements of all authorities with jurisdiction. Waste packaging should be recycled. Incineration or landfill should only be considered when recycling is not feasible. This material and its container must be disposed of in a safe way. Empty containers or liners may retain some product residues. Do not puncture or incinerate container.

Section 14. Transport information

	DOT Classification	IMDG	IATA
UN number	UN1950	UN1950	UN1950
UN proper shipping name	Aerosols, flammable (each not exceeding 1 L capacity)	Aerosols, flammable (each not exceeding 1 L capacity)	Aerosols, flammable (each not exceeding 1 L capacity)
Transport hazard class(es)	2.1 	2.1 	2.1 
Packing group	-	-	-
Environmental hazards	No.	No.	No.

AERG : 126

Special precautions for user : **Transport within user's premises:** always transport in closed containers that are upright and secure. Ensure that persons transporting the product know what to do in the event of an accident or spillage. Protect from freezing. Freezing will damage product and render it unusable.

Section 15. Regulatory information

- U.S. Federal regulations** : TSCA 8(a) PAIR: Decanal; Citronellal
United States inventory (TSCA 8b): All components are listed or exempted.
Clean Water Act (CWA) 311: Ammonia
Clean Air Act (CAA) 112 regulated flammable substances: Butane; Propane; Isobutane
- Clean Air Act Section 112 (b) Hazardous Air Pollutants (HAPs)** : Not listed
- Clean Air Act Section 602 Class I Substances** : Not listed
- Clean Air Act Section 602 Class II Substances** : Not listed
- DEA List I Chemicals (Precursor Chemicals)** : Not listed
- DEA List II Chemicals (Essential Chemicals)** : Not listed

SARA 302/304

Composition/information on ingredients

No products were found.

SARA 304 RQ : Not applicable.

SARA 311/312

Classification : FLAMMABLE AEROSOLS - Category 1
 GASES UNDER PRESSURE - Compressed gas
 SERIOUS EYE DAMAGE/ EYE IRRITATION - Category 2A

Composition/information on ingredients

Name	Classification
Isopropyl Alcohol	FLAMMABLE LIQUIDS - Category 2 SERIOUS EYE DAMAGE/ EYE IRRITATION - Category 2A SPECIFIC TARGET ORGAN TOXICITY (SINGLE EXPOSURE) (Narcotic effects) - Category 3

SARA 313

There is no data available.

State regulations

- Massachusetts** : The following components are listed: Isopropyl Alcohol; Butane; Propane; Isobutane
- New York** : None of the components are listed.
- New Jersey** : The following components are listed: Isopropyl Alcohol; Butane; Propane; Isobutane
- Pennsylvania** : The following components are listed: Isopropyl Alcohol; Butane; Propane; Isobutane
- California Prop. 65**

No products were found.

International lists

National inventory

- Australia** : All components are listed or exempted.
- Canada** : All components are listed or exempted.
- China** : All components are listed or exempted.

Section 15. Regulatory information

- Europe** : All components are listed or exempted.
New Zealand : All components are listed or exempted.
Philippines : All components are listed or exempted.
Republic of Korea : All components are listed or exempted.
Taiwan : All components are listed or exempted.

Section 16. Other information

Procedure used to derive the classification

Classification	Justification
FLAMMABLE AEROSOLS - Category 1 GASES UNDER PRESSURE - Compressed gas SERIOUS EYE DAMAGE/ EYE IRRITATION - Category 2A	On basis of test data Expert judgment Calculation method

History

- Date of issue mm/dd/yyyy** : 09/30/2018
Date of previous issue : 01/30/2018
Version : 2.1
Prepared by : KMK Regulatory Services Inc.

Notice to reader

To the best of our knowledge, the information contained herein is accurate. However, neither the above-named supplier, nor any of its subsidiaries, assumes any liability whatsoever for the accuracy or completeness of the information contained herein. Final determination of suitability of any material is the sole responsibility of the user. All materials may present unknown hazards and should be used with caution. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that exist.