

# ALBION<sup>®</sup>

## CASTERS AND WHEELS

# 68 Series Casters

- Precision Sealed Ball Bearing  
Eliminates Need For Routine Maintenance
- Yellow Zinc Chromate Finish
- Specifically Designed For Towing and Impact Applications Where Durability is Needed
- Non-Marking Wheels



68XP06228S



68PM06228R

**Applications:**Automotive Plants



**Overall Size:** 4-1/2" x 6-1/4"  
**Hole Soacing:** 2-7/16" x 4-15/16"  
 slotted to 3-3/8" x 5-1/4"  
**Bolt Dia.:** 1/2"



68PY06228S80A



68NX06228S

Wheel Dia. (In.)	Tread Width (In.)	Load Rating (lbs.)	Overall Height (In.)	Durometer	Wheel Bearing	Swivel Part Number	Rigid Part Number
<b>Solid Elastomer Polyurethane Wheel (Gray Tread)</b>							
6	2	1400	8-3/32	60 Shore D	Precision Ball	68XP06228S	68XP06228R
8	2	1200	10-1/4	60 Shore D	Precision Ball	68XP08228S	68XP08228R
<b>Round Polyurethane Tread on Aluminum Core Wheel (Green Tread)</b>							
6	2	1250	8-3/32	90 Shore A	Precision Ball	68PM06228S	68PM06228R
8	2	1500	10-1/4	90 Shore A	Precision Ball	68PM08228S	68PM08228R
<b>Thick Polyurethane Tread on Cast Iron Core Wheel (Tan Tread)</b>							
6	2	1050	8-3/32	80 Shore A	Precision Ball	68PY06228S80A	68PY06228R80A
8	2	1400	10-1/4	80 Shore A	Precision Ball	68PY08228S80A	68PY08228R80A
<b>Solid High Impact Polymer Wheel (Black Tread)</b>							
6	2	2000	8-3/32	80 Shore D	Precision Ball	68NX06228S	68NX06228R
8	2	2000	10-1/4	80 Shore D	Precision Ball	68NX08228S	68NX08228R