

## Low Profile Wraparound

### FEATURES

- Clear acrylic prismatic diffuser with flat bottom and vertical sides
- Two, three, or four-lamp cross sections
- Hinges from either side
- White steel end plates with flush knockouts for continuous row mounting
- Heavy gauge steel housing die embossed for maximum rigidity
- Heat sink embossments and levelling projections allow direct mounting of HPF fixtures on combustible low density cellulose fiberboard ceilings
- All metal parts are treated with a five stage phosphate bonding process and finished with a baked white enamel
- UL listed 1598, cUL or CSA. Damp Location standard



### ORDERING INFORMATION

MODEL	SIZE	NO. OF LAMPS IN CROSS SECTION	LAMP TYPE	BALLAST	VOLTAGE	OPTIONS
<b>AWN</b> 8 <sup>5</sup> / <sub>16</sub> " Wide	<b>2</b> 2' (AWN only)	<b>2</b> Two	<b>17</b> 2', T8: 17 Watt	<b>NOTE:</b> See Technical Section for other ballast options.	<b>U</b> 120V-277V	<b>EL</b> Emergency Battery Pack
<b>AWW</b> 14 <sup>5</sup> / <sub>8</sub> " Wide	<b>4</b> 4'	<b>3</b> Three	<b>28</b> 4', T5: 28 Watt	<b>E</b> Electronic Instant Start (Std.)	<b>347</b> 347V	<b>GLR</b> Fast Blow Fuse
	<b>8</b> 8'	<b>4</b> Four	<b>32</b> 4', T8: 32, 30, 28 or 25 Watt	<b>3E</b> 3-Lamp Electronic T8, Instant Start		<b>PAF</b> Paint After Fabrication
		See Product Availability table below.	<b>54</b> 4', T5HO: 54 Watt	<b>4E</b> 4-Lamp Electronic T8, Instant Start		<b>SB3</b> Stem Mounting Bracket (Required for 3-Lamp units only)
				<b>24E</b> (1) 2-Lamp and (1) 4-Lamp Electronic T8, Instant Start		<b>NYC</b> NYC Compliant
				<b>EP</b> Electronic T5 or T8, Programmed Start		<b>NYCU</b> NYC Compliant, Union Label
				<b>3EP</b> 3-Lamp Electronic T5HO or T8, Programmed Start		For more options see pages 96-112.
				<b>4EP</b> 4-Lamp Electronic T5HO (N/A 347V) or T8, Programmed Start		

### ACCESSORIES (ORDER SEPARATELY)

- S18** 18" Stem w/Canopy
- S518** 18" 45° Swivel Stem w/Canopy

### PRODUCT AVAILABILITY

SERIES	NO. OF LAMPS IN CROSS SECTION	NO. OF LAMPS IN FIXTURE	LAMP TYPE	LAMP LENGTH	WIDTH	LENGTH	HEIGHT
AWN2	2	2	17	2'	8 <sup>5</sup> / <sub>16</sub> "	2'	2 <sup>7</sup> / <sub>8</sub> "
AWN4	2	2	28, 32, 54	4'	8 <sup>5</sup> / <sub>16</sub> "	4'	2 <sup>7</sup> / <sub>8</sub> "
AWN8	2	4	28, 32, 54	4'	8 <sup>5</sup> / <sub>16</sub> "	8'	2 <sup>7</sup> / <sub>8</sub> "
AWW4	2	2	28, 32, 54	4'	14 <sup>5</sup> / <sub>8</sub> "	4'	2 <sup>25</sup> / <sub>32</sub> "
	3	3	28, 32, 54	4'	14 <sup>5</sup> / <sub>8</sub> "	4'	2 <sup>25</sup> / <sub>32</sub> "
	4	4	28, 32, 54	4'	14 <sup>5</sup> / <sub>8</sub> "	4'	2 <sup>25</sup> / <sub>32</sub> "
AWW8	2	4	28, 32, 54	4'	14 <sup>5</sup> / <sub>8</sub> "	8'	2 <sup>25</sup> / <sub>32</sub> "
	3	6	28, 32, 54	4'	14 <sup>5</sup> / <sub>8</sub> "	8'	2 <sup>25</sup> / <sub>32</sub> "
	4	8	28, 32, 54	4'	14 <sup>5</sup> / <sub>8</sub> "	8'	2 <sup>25</sup> / <sub>32</sub> "

