

HIGH-SPEED VERTICAL HAND DRYER

TECHNICAL data sheet

HIGH-SPEED VERTICAL HAND DRYER

19UC76 is a 'hands in' vertical style high speed hand dryer featuring a HEPA filter system, wider hand drying cavity opening and antimicrobial technology. Dedicated water collection reservoir eliminates water from collecting on the floor resulting in reduced maintenance. Polarized plug for easy installation eliminating the need to hard wire. Quiet operation is ideal for sound sensitive areas.



PRODUCT FEATURES AND BENEFITS

- 10 - 12 second dry time
- 25% greater hand drying cavity opening provides comfortable dry without touching sides of hand dryer
- HEPA filter with odor neutralizing tablet reduces contaminants in the air when hand drying*
- Water collection reservoir eliminates water from collecting on the floor resulting in reduced maintenance**
- LED display indicates when to empty water tray and change HEPA filter for easy maintenance
- Quiet operation ideal for sound sensitive areas
- ADA compliant
- Simple mounting bracket with polarized plug for easy installation
- Antimicrobial technology inhibits the growth of bacteria, mold and fungus and extends the dryer's service life
- Automatic operation promotes hand hygiene
- Durable and vandal resistant
- IP33 ingress protection against water




PRODUCT SPECIFICATIONS

	110-120 V
Amps	10
Watts	1200
Hz	60 Hz

DRYER SIZES:

Unit Size (HxWxD) - 13" x 26.25" x 9.25"
Shipping Size (HxWxD) - 16" x 28.5" x 12"
Unit Weight - 19.5 lbs
Shipping Weight - 25 lbs




LED DISPLAY

The LED display provides information about the operation and servicing needs of the hand dryer.

- LED's 1 through 4 flash Green when dryer is in operation.
- LED 5 is solid Green when dryer is in standby mode; solid Blue when dryer is in operation.
- LED 6 is unlit during normal operation; flashing Red when HEPA filter requires replacement.
- LED 7 is unlit during normal operation; solid Blue when water collection tank needs emptying.

PRODUCT DIMENSION DRAWINGS



CERTIFICATION APPROVED



IP33

SKU NO.	NOZZLE TYPE	COVER MATERIAL	COVER FINISH	OPERATION	VOLTAGE	AMPS	DRY TIME
DAYTON SURFACE-MOUNTED ADA COMPLIANT HAND DRYER							
19UC76	Vertical hand-in	High Impact ABS	Silver	Automatic	120 V	10	10-12 sec.

Find it at Grainger.

Call or visit your local branch or go to grainger.com/dayton for complete product line information.

Dayton[®]