



The bright white radiance of the GE energy smart® LED retail PAR30 short and long neck lamps is not just something you see, it's something you feel.

GE energy smart® LED retail PAR30 short and long neck lamps

PERFORMANCE DATA

BULB SHAPE	BASE TYPE	WATTS	GRAINGER ITEM NUMBER	ORDER CODE	DESCRIPTION	VOLTS	CASE QTY ⁽¹⁾	MOL (IN)	LUMENS INITIAL	CBCP	COLOR TEMP	INITIAL CRI	+RATED LIFE (YRS) 3HRS/DAY	*RATED LIFE (70HRS)	*ESTIMATED ENERGY COST/YR	ENERGY STAR® STATUS	ADDITIONAL INFORMATION
Retail PAR30 - Dimming (Visual Comfort Lens™)																	
PAR30	MED	12	36M976	67922	LED12DP30R930/15	120	6	3.75	860	5650	3000	91	22.8	25,000	\$1.45	★	Accent, 15° Beam, Silver
			36M977	67923	LED12DP30R930/25	120	6	3.75	860	3100	3000	91	22.8	25,000	\$1.45	★	Accent, 25° Beam, Silver
			36M978	67924	LED12DP30R930/40	120	6	3.75	860	1350	3000	91	22.8	25,000	\$1.45	★	Accent, 40° Beam, Silver
			36M973	67925	LED12DP30R927/15	120	6	3.75	820	5350	2700	91	22.8	25,000	\$1.45	★	Accent, 15° Beam, Silver
			36M974	67926	LED12DP30R927/25	120	6	3.75	820	2950	2700	91	22.8	25,000	\$1.45	★	Accent, 25° Beam, Silver
Retail PAR30 Long Neck - Dimming (Visual Comfort Lens™)	MED	12	36M975	67927	LED12DP30R927/40	120	6	3.75	820	1300	2700	91	22.8	25,000	\$1.45	★	Accent, 40° Beam, Silver
			36M983	68387	LED12DP3LR930/15	120	6	4.75	860	5650	3000	91	22.8	25,000	\$1.45		Accent, 15° Beam, Silver
			36M984	68388	LED12DP3LR930/25	120	6	4.75	860	3100	3000	91	22.8	25,000	\$1.45		Accent, 25° Beam, Silver
			36M985	68389	LED12DP3LR930/40	120	6	4.75	860	1350	3000	91	22.8	25,000	\$1.45		Accent, 40° Beam, Silver
			36M980	68390	LED12DP3LR927/15	120	6	4.75	820	5350	2700	91	22.8	25,000	\$1.45		Accent, 15° Beam, Silver
Retail Display Compact PAR30 Long Neck - Non-Dimming (High CRI - Low Glare - Visual Comfort Lens™)	MED	12	36M981	68391	LED12DP3LR927/25	120	6	4.75	820	2950	2700	91	22.8	25,000	\$1.45		Accent, 25° Beam, Silver
			36M982	68392	LED12DP3LR927/40	120	6	4.75	820	1300	2700	91	22.8	25,000	\$1.45		Accent, 40° Beam, Silver
			16X191	66050	LED12P3LS930/25	120	6	4.75	660	3000	3000	92	22.8	25,000	\$1.45	★	Narrow Flood, 25° Beam, Silver
			16X192	66051	LED12P3LS930/40	120	6	4.75	660	950	3000	92	22.8	25,000	\$1.45	★	Flood, 40° Beam, Silver
			16X193	66052	LED12P3LS927/25	120	6	4.75	630	3000	2700	92	22.8	25,000	\$1.45	★	Narrow Flood, 25° Beam, Silver
			16X194	66053	LED12P3LS927/40	120	6	4.75	630	900	2700	92	22.8	25,000	\$1.45	★	Flood, 40° Beam, Silver

* The life rating is based on the hours of operation the lamp will provide before reaching 70% of its original lumen rating (L70)
** Minimum order quantity = 6
★ ENERGY STAR® qualified
^ Estimated energy cost per year based on \$0.11 per kWh energy rate and 3 operating hours per day
Note: Product descriptions ending in "TP" indicate a card blister or clamshell package nested in a tray for shelf display.
Cards also designed for hook display.



For additional product and application information, visit
www.gelighting.com/ThinkLED

Information provided is subject to change without notice. Please verify all details with GE. All values are design or typical values when measured under laboratory conditions, and GE makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.




Product is compliant with material restriction requirements of RoHS
energy smart® is a registered trademark of GE
ENERGY STAR® and the ENERGY STAR® logo are registered U.S. marks




Information provided is subject to change without notice. Please verify all details with GE. All values are design or typical values when measured under laboratory conditions, and GE makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.

CHROMATICITY DIAGRAM




SPECTRAL POWER DISTRIBUTION




40° BEAM

POLAR PLOT—40° BEAM




CONE DIAGRAM




25° BEAM

POLAR PLOT—25° BEAM



CONE DIAGRAM



For additional product and application information, visit

www.gelighting.com/ThinkLED

Information provided is subject to change without notice. Please verify all details with GE. All values are design or typical values when measured under laboratory conditions, and GE makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.

For additional product and application information, visit

www.gelighting.com/ThinkLED

Information provided is subject to change without notice. Please verify all details with GE. All values are design or typical values when measured under laboratory conditions, and GE makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.