

brighten



The versatile brightness of GE's LED MR16 lamps is not just something you see, it's something you feel.

LED MR16 lamps

For high-output in decorative lighting applications, GE's dimmable 7-watt LED MR16 lamp is the perfect solution.

LOW-COST OPERATION

- For example, using only 7 watts of energy, save over \$118 in energy costs over the rated life of a lamp versus a standard 50-watt halogen lamp based on \$0.11 per kWh
- Energy efficiency and long life mean fewer lamp replacements versus halogen MR16 light sources

EXCELLENT COLOR RENDERING

- Available with a CRI of 80 - 87

COLOR TEMPERATURE

- Halogen-like color
- Available in 2700K, 3000K and 4000K

LONG LIFE

- Up to 25,000 hours rated life (L70)

DIMMABLE

- Dims from 100% to 10%

BEAM PATTERNS

- Available in 15°, 25° and 35° beam patterns

TRANSFORMER COMPATIBILITY

- A lamp-transformer compatibility table has been developed and is available at www.gelighting.com/LED-MR16

ENVIRONMENTALLY CONSCIOUS

- These lamps are energy efficient, contain no lead or mercury, and are compliant with material restriction requirements of RoHS

GE QUALITY AND RELIABILITY

- 3-year limited warranty

To learn more about saving money and energy, go to: gelighting.com/ThinkLED

When you Think LED lighting, Think GE.

ecomaginationSM



imagination at work

Information provided is subject to change without notice. Please verify all details with GE. All values are design or typical values when measured under laboratory conditions, and GE makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.

LED MR16 lamps

Directional Lamps (MR16)

Bulb Shape	Base Type	Watts	Order Code	Description	Volts	Case Qty**	MOL (In)	Lumens Initial	CBCP	Initial Color Temp	CRI	Wattage Equivalent	*Rated Life L70 (Hrs)	Dimmable	ENERGY STAR® Status	#Location Rating	Additional Information	
12 Volt AC/DC MR16																		
MR16		7	69919	LED7DMR16D830/15	12	6	1.9	390	3700	3000	85	35W	25,000	Yes	★	Dry	Accent, 15° beam, Silver, Gen 2	
			69920	LED7DMR16D830/25	12	6	1.9	390	1900	3000	83	35W	25,000	Yes	★	Dry	Accent, 25° beam, Silver, Gen 2	
			69921	LED7DMR16D830/35	12	6	1.9	390	1100	3000	83	35W	25,000	Yes	★	Dry	Accent, 35° beam, Silver, Gen 2	
			69922	LED7DMR16D827/15	12	6	1.9	370	3500	2700	83	35W	25,000	Yes	★	Dry	Accent, 15° beam, Silver, Gen 2	
			69923	LED7DMR16D827/25	12	6	1.9	370	1800	2700	83	35W	25,000	Yes	★	Dry	Accent, 25° beam, Silver, Gen 2	
			69924	LED7DMR16D827/35	12	6	1.9	370	1000	2700	83	35W	25,000	Yes	★	Dry	Accent, 35° beam, Silver, Gen 2	
			69925	LED7DMR16D840/15	12	6	1.9	430	4000	4000	87	35W	25,000	Yes	★	Dry	Accent, 15° beam, Silver, Gen 2	
			69926	LED7DMR16D840/25	12	6	1.9	430	2100	4000	84	35W	25,000	Yes	★	Dry	Accent, 25° beam, Silver, Gen 2	
			69927	LED7DMR16D840/35	12	6	1.9	430	1200	4000	84	35W	25,000	Yes	★	Dry	Accent, 35° beam, Silver, Gen 2	
			69949	LED7XDMR16D83025	12	6	1.9	500	2500	3000	82	50W	25,000	Yes	★	Dry	Accent, 25° beam, Silver	
			69950	LED7XDMR16D83035	12	6	1.9	500	1500	3000	82	50W	25,000	Yes	★	Dry	Accent, 35° beam, Silver	
			69951	LED7XDMR16D82725	12	6	1.9	480	2400	2700	80	50W	25,000	Yes	★	Dry	Accent, 25° beam, Silver	
			69952	LED7XDMR16D82735	12	6	1.9	480	1400	2700	80	50W	25,000	Yes	★	Dry	Accent, 35° beam, Silver	

Get more information at
GELighting.com/ThinkLED

Information provided is subject to change without notice. Please verify all details with GE. All values are design or typical values when measured under laboratory conditions, and GE makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.

* The life rating is based on the hours of operation the lamp will provide before reaching 70% of its original rating (L70)

** Minimum order quantity = 6

★ ENERGY STAR® status: Certified as meeting ENERGY STAR® guidelines.

UL 1993 Environmental Requirements for LED LAMPS

Location, damp - Exterior or interior location that is normally or periodically subject to condensation of moisture in, on, or adjacent to, electrical equipment, and includes partially protected locations.

Location, dry - Location not normally subject to dampness, may include a location subject to temporary dampness, i.e., building under construction, provided ventilation is adequate to prevent an accumulation of moisture.

Location, wet - Location in which water or other liquid can drip, splash, or flow on or against electrical equipment.

^ Incandescent or Halogen wattage equivalencies based on ENERGY STAR® guidelines using lumens or CBCP according to lamp type

Notes: 1) Product descriptions ending in "JTP" indicate a carded blister or clamshell package nested in a tray for shelf display. Cards also designed for hook display.
 2) LED A19 Locking device works on PC: 85791, 85792, 89898, 62182, 89899 and 89900



Product is compliant with material restriction requirements of RoHS

ENERGY STAR® and the ENERGY STAR® logo are registered U.S. marks

ecomaginationSM



www.gelighting.com

GE and the GE Monogram are trademarks of the General Electric Company. All other trademarks are the property of their respective owners. Information provided is subject to change without notice. All values are design or typical values when measured under laboratory conditions. GE Lighting and GE Lighting Solutions, LLC are businesses of the General Electric Company. © 2015 GE.

65027 | Rev 3/4/15