

illuminate



The bright white radiance of GE's LED A-Line lamps is not just something you see, it's something you feel.

LED A-Line general purpose lamps

GE offers dimmable LED A-Line lamps as excellent replacements for standard 25-watt, 40-watt, 60-watt, 75-watt and 100-watt incandescent lamps.

LOW-COST OPERATION

- For example, a 60-watt incandescent replacement lamp using 13 watts of energy and producing 800 lumens can save over \$129 in energy costs over the rated life of the lamp versus a standard 840 lumen, 60-watt incandescent A19 based on \$0.11 per kWh
- Energy efficiency and long life mean fewer lamp replacements versus standard incandescent or halogen light sources

EXCELLENT COLOR RENDERING

- Available with a CRI of 78 - 90

COLOR TEMPERATURE

- Halogen-like color
- Available in 2700K, 3000K and 5000K

LONG LIFE

- Up to 25,000 hours rated life (L70)

DIMMABLE

- Dims from 100% to as low as 10%

ENVIRONMENTALLY CONSCIOUS

- These lamps are energy efficient, contain no lead or mercury, and are compliant with material restriction requirements of RoHS

GE QUALITY AND RELIABILITY

- 3-year limited warranty

To learn more about saving money and energy, go to: gelighting.com/ThinkLED

When you Think LED lighting, Think GE.

ecomaginationSM



imagination at work

Information provided is subject to change without notice. Please verify all details with GE. All values are design or typical values when measured under laboratory conditions, and GE makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.

LED A-Line general purpose lamps

A-Line Lamps

Bulb Shape	Base Type	Watts	Grainger Item Number	Order Code	Description	Volts	Case Qty**	MOL (in)	Lumens Initial	CBCP	Initial Color Temp	CRI	Wattage Equivalent	*Rated Life L70 (Hrs)	Dimmable	ENERGY STAR® Status	#Location Rating	Additional Information		
A-15																				
	MED	3	6XWK4	63011	LED3A15/W/TP	120	3	3.5	120		3000	80	-	15,000	-		Dry	White		
				63012	LED3A15/C/TP	120	3	3.5	120		3000	80	-	15,000	-		Dry	Clear		
	MED	4.5	22MX10	68173	LED4DA15-W/TP	120	3	3.5	270		2700	82	25W	15,000	Yes		Damp	White		
				68174	LED4DA15-C/TP	120	3	3.5	270		2700	82	25W	15,000	Yes		Damp	Clear		
				36GJ36	14644	LED4.5DA15-C/827	120	6	3.5	300		2700	80	40W	15,000	Yes		Damp	Clear	
A-19																				
	MED	7	40D437	14063	LED7DAV3/827W	120	6	4.6	470		2700	80	40W	25,000	Yes		Damp	White, Semi-Omni		
				36GJ38	95928	LED7DAV3/5K	120	6	4.6	500		5000	80	40W	25,000	Yes		Damp	White, Semi-Omni	
				36GJ37	11332	LED7DA19/827	120	6	4.4	450		2700	80	40W	25,000	Yes	★	Damp	White, Omnidirectional	
				71208	LED7DA19/830	120	6	4.4	450		3000	80	40W	25,000	Yes	★	Damp	White, Omnidirectional		
	11	32WX16	11328	LED11DA19/827	120	6	4.4	800		2700	80	60W	25,000	Yes	★	Damp	White, Omnidirectional			
					71209	LED11DA19/830	120	6	4.4	800		3000	80	60W	25,000	Yes	★	Damp	White, Omnidirectional	
					40D436	13791	LED11DAV3/827W	120	6	4.6	800		2700	80	60W	15,000	Yes		Damp	White, Semi-Omni
					95927	LED11DAV3/5K	120	6	4.4	800		5000	80	60W	15,000	Yes		Damp	White, Semi-Omni	
A-Line Reveal																				
	MED	8	36GJ39	69220	LED8DA19RVL/TP	120	3	4.4	430		2700	90	40W	25,000	Yes		Damp	White, Semi-Omni		
				11	36GJ40	69204	LED11DA19RVL/TP	120	3	4.4	680		2700	90	60W	15,000	Yes		Damp	White, Semi-Omni
A-21																				
	MED	13	14075	14075	LED13DA21/827	120	6	5.3	1100		2700	80	75W	25,000	Yes	★	Damp	White, Omnidirectional		
				14	94936	LED14DA21/827W	120	6	5.3	1100		2700	80	75W	15,000	Yes		Damp	White, Semi-Omni	
				16	32WX12	14074	LED16DA21/827	120	6	5.3	1600		2700	80	100W	25,000	Yes	★	Damp	White, Omnidirectional
						34236	LED16DA21/830	120	6	5.3	1600		3000	80	100W	25,000	Yes	★	Damp	White, Omnidirectional
				17	16113	LED17DA21/827	120	6	5.3	1600		2700	78	100W	15,000	Yes		Damp	White, Semi-Omni	
Locking Device																				
				62182	LED A19 LOCK DEV ²													White, Kit		

Get more information at GELighting.com/ThinkLED

Information provided is subject to change without notice. Please verify all details with GE. All values are design or typical values when measured under laboratory conditions, and GE makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.

* The life rating is based on the hours of operation the lamp will provide before reaching 70% of its original rating (L70)

** Minimum order quantity = 6

★ ENERGY STAR® status. Certified as meeting ENERGY STAR® guidelines.

UL 1993 Environmental Requirements for LED LAMPS

Location, damp - Exterior or interior location that is normally or periodically subject to condensation of moisture in, on, or adjacent to, electrical equipment, and includes partially protected locations.

Location, dry - Location not normally subject to dampness, may include a location subject to temporary dampness, i.e., building under construction, provided ventilation is adequate to prevent an accumulation of moisture.

Location, wet - Location in which water or other liquid can drip, splash, or flow on or against electrical equipment.

^ Incandescent or Halogen wattage equivalencies based on ENERGY STAR® guidelines using lumens or CBCP according to lamp type

Notes: 1) Product descriptions ending in "7TP" indicate a carded blister or clamshell package nested in a tray for shelf display. Cards also designed for hook display.
2) LED A19 Locking device works on PC: 85791, 85792, 89898, 62182, 89899 and 89900



Product is compliant with material restriction requirements of RoHS

ENERGY STAR® and the ENERGY STAR® logo are registered U.S. marks

ecomaginationSM



www.gelighting.com

GE and the GE Monogram are trademarks of the General Electric Company. All other trademarks are the property of their respective owners. Information provided is subject to change without notice. All values are design or typical values when measured under laboratory conditions. GE Lighting and GE Lighting Solutions, LLC are businesses of the General Electric Company. © 2015 GE.

63563-G (Rev 4/2/15)

Distributor:

