



Connectors > Rectangular Connectors > Rectangular Connector Hoods & Bases



Hood & Base Connector Product Type: **Base Housing**

Cable Entry Location: **Bottom**

Hood & Base Locking Device Type: **Locking**

Sealable: **Yes**

Circuit Application: **Power & Signal**

Features

Product Type Features

Product Size	4
Hood & Base Connector Product Type	Base Housing
Sealable	Yes

Body Features

Material	Die Cast Aluminum
Cable Entry Location	Bottom

Mechanical Attachment

Locking Device Location	Housing
Hood & Base Locking Device Type	Locking

Usage Conditions

Corrosion Protected	Yes
---------------------	-----

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Packaging Features

Packaging Method	Box
------------------	-----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (.35% in Component) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # T1310100116-000 H10B-TS-RO-PG16	 TE Part # T2040102201-000 HE-010-F	 TE Part # T1310100120-000 H10B-TS-RO-M20	 TE Part # T1320100116-000 H10B-TG-RO-PG16
 TE Part # T1320100120-000 H10B-TG-RO-M20	 TE Part # T1320100125-000 H10B-TG-RO-M25	 TE Part # T1330100120-000 H10B-TSH-RO-M20	 TE Part # T1330100121-000 H10B-TSH-RO-PG21



 TE Part # T1330100125-000 H10B-TSH-RO-M25	 TE Part # T1330100132-000 H10B-TSH-RO-M32	 TE Part # T1340100121-000 H10B-TGH-RO-PG21	 TE Part # T1340100125-000 H10B-TGH-RO-M25
 TE Part # T1340100132-000 H10B-TGH-RO-M32	 TE Part # T1310100121-000 H10B-TS-RO-PG21	 TE Part # T1330100129-000 H10B-TSH-RO-PG29	 TE Part # T1300100216-000 H10B-TS/G-RO-2PG16
 TE Part # T1300100225-000 H10B-TS/G-RO-2M25	 TE Part # T1300100313-000 H10B-TG/TS-RO-3PG13.5	 TE Part # T1310100016-000 H10B-TS-RO-M16	 TE Part # T1310100113-000 H10B-TS-RO-PG13.5

Also in the Series | [HDC IP65](#)



Rectangular Connector Hoods & Bases
(1258)

Documents

[Product Drawings](#)
[H10B-AG-LB](#)

English

- [CAD Files](#)
- [3D PDF](#)
- [3D](#)
- [Customer View Model](#)



[ENG_CVM_CVM_T1500103000-000_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_T1500103000-000_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_T1500103000-000_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Heavy Duty Connectors](#)

English

[HEAVY DUTY CONNECTORS](#)

English

Product Specifications

[Application Specification](#)

English