


WHATEVER.



WHEREVER.



WHENEVER.



→ Right. Now.

Get the message right...and get it out now with the GlobalMark® 2 Industrial Label Maker.

The GlobalMark® 2 Industrial Label Maker gives you the power to produce whatever professional signs and labels you need, wherever and whenever you need them.

A visual workplace- There is no substitute for a specific message that clearly delivers critical information, at the precise point of need. The GlobalMark 2 Printer plays a critical role in many lean programs including 5S, Standard Work, Total Productive Maintenance, Quick Changeover, Kanban etc.

As a result you:

- Improve Safety
- Enhance Productivity
- Reduce Costly Errors
- Increase Profitability

The GlobalMark 2 Printer helps ensure that lean and six sigma improvements remain clearly visible, readily understood and consistently adhered to, long after programs are initiated.

Exactly the message you need, when you need it. When you need a sign or label, you need it now – you don't want to wait a day or a week for a custom order. With the GlobalMark® 2 Industrial Label Maker Wizards, just touch, print, and get the message you need – right now – with built-in templates, graphics, and applications for:

- Pipe Markers
- Arc Flash Labels
- LO/TO Instructions
- Electrical Circuit ID
- OSHA and ANSI Warnings
- Machine Guard Labels
- Warehouse and Inventory Labels
- Glow-in-the-Dark Emergency Exit Markings
- General Facility ID and Signs





Easy, versatile, customized signs and labels.

The GlobalMark® 2 Industrial Label Maker gives you built-in templates, graphics, and applications, so you can quickly and easily create pipe markers, safety signs, hazardous labels, tags, equipment and warehouse marking, and more.

You can even create custom templates!

The features you need at your fingertips:

- English, Spanish, French Languages Built In
- Print Size .08" to 3.8"
- 5 Fonts Built In
- Bar Codes 128, 39 and Int. 2 of 5 Built In
- Tape Widths 1/2" to 4"
- Clear Label Preview Before Printing
- Large Color Touch Screen
- Full Size Keyboard
- XY Axis Plotter/Cutter on Color & Cut Model
 - Die cuts .08" to 3.8"
- Compact Flash Memory Card Port
- Sharp 300 DPI Print Resolution
- Touch-and-Drag Editing
- Stand-Alone Operation or PC-Connect Operation (see next page for PC-Connect operation & software options)

Key Functions:

- Multiple Color Printing
- Bold**
- Underline
- Italics*
- Superscript/Subscript

- Reverse Print**
- Auto Fit To Specific Length
- Frames Automatically**
- Justify Text Automatically
- Expand/Condense


Vertical

Specifications:

Physical characteristics – Size: 10" high x 16" wide x 11" deep
 Weight: approximately 30 pounds/13.6 kg

Environmental characteristics – Operational requirements:

Ambient operating temperature: 50°F to 105°F (10°C to 41°C)
 Relative humidity: 20% to 80% (non-condensing)



More Options.

Operate your GlobalMark® Industrial Label Maker in PC-Connect mode and get more options and label-making muscle!

In addition to the robust stand-alone capabilities of the GlobalMark® Industrial Label Maker, you get even more options when you operate your GlobalMark® Industrial Label Printer from one of Brady's powerful PC software programs:

MarkWare™ EXPRESS Software

The ultimate sign database – get your message out even faster with MarkWare™ EXPRESS.

MarkWare™ EXPRESS Software contains thousands of pre-made pipe markers, OSHA signs, and labels ready to print as-is or customize with a click of your mouse! Fast. Accurate. Amazing!

- Signs, labels, tags, pipe markers and more - all pre-made and ready to print or customize
- Thousands of stock legends
- High-speed search gives you instant access
- OSHA and ANSI sign formats, ANSI-ASME Pipe Markers
- Contains French and Spanish legends too!

MarkWare Deluxe & MarkWare™ Lean Tools

Expand your sign- and label-making capabilities with MarkWare™ Deluxe or MarkWare™ LEAN Facility Identification Software.

The GlobalMark 2 printer and MarkWare Software give you more design options and expanded custom features, plus an extensive library of ready-to-print, customizable label, tag, and sign templates.




- Chemical database for faster, more accurate, Right-To-Know signs and labels.
- Import information from your database or spreadsheet
- Import your own full-color images.
- Over 1,000 safety symbols and industrial pictograms for virtually any application.
- Templates specifically designed to meet Arc Flash and Egress/Fire identification requirements.
- Identify normal machine operations at a glance using printed gauge and magnahelic gauge labels (lean version only)

Description	Part No.
MarkWare™ EXPRESS Software	20700X
MarkWare™ Deluxe Software	20700
MarkWare™ Lean Tools Software	20700L

MarkWare™ EXPRESS Software Signs and Labels Database



MarkWare™ Facility Identification Software





ChemLabel™
Hazardous Material
Labeling Software



**ChemLabel™ Hazardous Material
Labeling Software**

Help Keep Employees Safe with ChemLabel™ Hazardous Material Labeling Software. Poorly or inaccurately labeled chemicals and dangerous materials represent potentially serious safety problems.

Brady's ChemLabel Software features on-screen wizards that let you link from a chemical database to a label layout, helping ensure accurate label information. Pre-designed templates, editing and drawing tools, and a connection to Brady industrial supplies help you easily create and print durable, informative chemical labels.



Lockout PRO™
Graphical Procedure
Writing Software
*Print procedure, tag, and
energy source labels.*

Lockout Pro™ Software

OSHA Compliance Made Easy with Lockout PRO™ Graphical Procedure Software. With the GlobalMark® 2 Printer and Lockout PRO Software, you can create lockout procedure tags, labels, and energy source identification in just three minutes! This helps you:

- Increase employee safety.
- Increase productivity with more efficient lockout/tagout operations.
- Avoid costly OSHA fines.




Quicklabel Application Card

Premade Signs and Labels in PCMCIA card format.

- Ready to print format is error free and hassle free.
- Text is editable.
- Three easy steps:
 1. Enter the corresponding code from the QuickLabel guide.
 2. Scroll through the list to select your template while previewing your label.
 3. Print to your GlobalMark 2 printer.



**QuickLabel
Application Card**



Description	Part No.
ChemLabel™ Hazardous Material Labeling Software	50987
Lockout Pro™ Software	LOPDESK1001
Quicklabel Application Card	102741

Start Now

Three Models. Unlimited Potential. Get the features you need with these GlobalMark® 2 printer models. Get one of Brady's optional label-making software programs for even more customizable templates and other options.

Color & Cut System

- Prints in one color, multiple spot colors, and blended colors.
- Built-in label cutter, plus a plotter cutter for cutting out images, numbers, and letters.
- With Brady's MarkWare™ software program, import and print full-color logos, art, and even photos.
- Supply Saver Feature.

MultiColor System

- The same color options as the Color & Cut system, without the plotter cutter.

MonoColor System

- Prints one color on one color tape.

GlobalMark® 2 Industrial Label Maker	Part No.
GlobalMark 2 MonoColor	76798
GlobalMark 2 MultiColor	76800
GlobalMark 2 Color & Cut	76801

GlobalMark ships with a keyboard, power cord, cleaning kit, USB cable, and Brady File Management Utility.



Keep your GlobalMark® Industrial Label Printer working for you with a Brady 360 Printer Protection & Care Plan. Choose from two Brady 360 coverage levels with the purchase of a GlobalMark® 2 Industrial Label maker:

Basic Plan:

- Extended Warranty – Two full years added to the basic six-month warranty for a total of 30 months. Add another six months by registering your printer online – a full three years of warranty coverage!
- Free Loaner Printer – In the event that your GlobalMark® Industrial Label Maker ever requires service, you'll stay productive with the use of a free loaner GlobalMark® Industrial Label Maker from Brady.


Preferred Plan:

- Same extended warranty and loaner as in Basic Plan, plus...
- Free Preventive Maintenance Service – After two years we'll evaluate the operation of your printer to make sure it's working the best for you, clean all its moving parts and replace any wearable parts as needed other than the print-head.
- Free Printer Firmware Upgrades – Covers firmware-only upgrades.
- Two Free Hours of Brady 360 Extended Professional Tech Services – Includes services such as template creation, label conversion service, extended on-phone training, database integration support, 3rd party software integration assistance and more!



GlobalMark® 2 Industrial Label Maker	Part No.
GlobalMark 2 MonoColor printer with Brady 360 Basic Plan	114449
GlobalMark 2 MonoColor printer with Brady 360 Preferred Plan	114454
GlobalMark 2 MultiColor printer with Brady 360 Basic Plan	114450
GlobalMark 2 MultiColor printer with Brady 360 Preferred Plan	114455
GlobalMark 2 Color & Cut printer with Brady 360 Basic Plan	114451
GlobalMark 2 Color & Cut printer with Brady 360 Preferred Plan	114456

Performance.



Our print ribbons are easy to load – just drop them in and go. Brady print ribbons come in a protective, easy-to-load cartridge that makes the GlobalMark® 2 printer even easier to use. Choose single or multicolor ribbons for your specific applications and printer.

Single Color Print Ribbon Cartridges – 200 ft./roll

Color	4.11" x 200 ft. Part No.
● Black	76739
● Black for Preprinted RTK Supplies	96089
○ White	76741
● Red	76743
● Blue	76745
● Green	76747
● Magenta	76749
● Yellow	76751
● Orange	76752
● Process Cyan	76759
● Process Yellow	76760
● Process Magenta	76761



NFPA



Color Bar



HMIG



NFR

Right-to-Know Die Cut Labels (Vinyl)

	Label Size	Part No.
NFPA diamond only (300/roll)	4" square	76729
NFPA diamond only (530/roll)	2.25" x 2.25"	51861
RTK w/color bar (530/roll)	2.25" x 2.25"	51854
RTK w/color bar (300/roll)	2.25" x 4"	76730
RTK w/color bar (200/roll)	4" x 6"	76731
RTK w/NFPA diamond (530/roll)	2.25" x 2.25"	51860
RTK w/NFPA diamond (300/roll)	2.25" x 4"	76732
RTK w/NFPA diamond (200/roll)	4" x 6"	76733
HMIG Label color bar only (530/roll)	2.25" x 2.25"	76734
HMIG Label Format 2 (400/roll)	1.125" x 3"	76735
NFR Label (400/roll)	1.125" x 3"	76736

Must use RTK ribbon (96089).

Hand-Applied Overlaminates for RTK Labels (B – 574)

Size	Quantity Per Pkg.	Part No.
1.5" x 2.5"	50	64984
2.5" x 2.5"	50	58476
3.5" x 5.5"	50	58706
4.5" x 6.5"	50	64985
7.5" x 10.5"	50	58708

Two Color Print Ribbon Cartridges – 200 ft./roll

(Not available for MonoColor)	4.11" x 8" Panels Part No.	4.11" x 16" Panels Part No.
●● Black and Red	76763	76762
●● Black and Blue	76775	76774
●● Black and Yellow	76767	76766
●● Black and Orange	76771	76770
●● Black and Green	76779	76778
●● Red and Blue	-	76782
●● Red and Green	110220	-

Typical yield from 2-color ribbons: 100-8in labels from 8" paneled ribbon; 60-16in labels from 16" paneled ribbon.

Four Color Print Ribbon Cartridges – 200 ft./roll

(Not available for MonoColor)	4.11" x 8" Panels Part No.	4.11" x 16" Panels Part No.
●●●● Black/Orange/Red/Blue	51447	-
●●●● Black/Red/Blue/Green	76787	76786
●●●● Black/Red/Blue/Yellow	76791	76790
●●●● Cyan/Magenta/Yellow/Black	76795	76794
●●●● Black/Red/Green/Yellow	110221	-


Typical yield from 4-color ribbons: 50-8in labels from 8" paneled ribbon; 30-16in labels from 16" paneled ribbon

Accessories

	Part No.
Hand Carrying Case w/wheels	76802
Mouse	76808
Serial Cable	76805
Stylus Pens (3 pack)	76809
256MB Memory Card	76810
Replacement Cutting Blade	76811
Transfer Tape (4.25" x 200 ft.)	76737
Grommets for Tags (100/pk)	20596
Hole Punch for Tags	20591
8" Nylon Cable Ties (100/pk)	81762
Weeding Tool	36611
Squeegee	36612

White Vinyl Preprints (B – 588) – 100 ft./roll


Color	2.25" (1" Stripe)	3" (1" Stripe)	4" (1" Stripe)	4" (3/4" Stripe)
● Red Stripe	101944	101946	101948	104068
● Orange Stripe	101945	101947	101949	104069
● Yellow Stripe	105043	105044	105045	-



Software

	Part No.
Surf on Signs™ Label Database	98200
MarkWare™ Facility Identification Software	20700
MarkWare™ 3.7 LEAN Facility Identification Software	20700L
Lockout Pro™ 3.0 Graphical Procedure Writing Software	LOPBASIC31001
ChemLabel™ Hazardous Material Labeling Software	50987
QuickLabel Application Card	102741

With Brady Quality.



The materials you need for any application.

Brady offers the industrial-grade materials you need to put any message, anywhere. Tags, glow-in-the-dark labels, reflective labels, magnetic labels, static cling signs, pipe markers, and more.

Indoor/Outdoor Vinyl Tape – 100 ft./roll

Color	4" Wide Part No.	3" Wide Part No.	2.25" Wide Part No.	1.125" Wide Part No.	0.5" Wide Part No.
Clear	97734	N/A	97735	97736	97737
White	76542	76543	76544	76545	76546
Yellow	76547	76548	76549	76550	76551
Red	76552	N/A	76553	76554	76555
Green	76556	N/A	76557	76558	76559
Blue	76560	N/A	76561	76562	76563
Black	76564	N/A	76565	76566	76567
Brown	76568	N/A	76569	76570	76571
Gold	76572	N/A	76573	76574	76575
Grey	76576	N/A	76577	76578	76579
Purple	76590	N/A	76591	76592	76593
Orange	76594	N/A	76595	76596	76597

Polyester Tape (B – 569) – 100 ft./roll

Color	4" Wide Part No.	3" Wide Part No.	2.25" Wide Part No.	1.125" Wide Part No.	0.5" Wide Part No.
Clear	76610	N/A	76611	76612	76613
White	76614	76615	76616	76617	76618
Yellow	76619	N/A	76620	76621	76622
Red	76623	N/A	76624	76625	76626
Blue	76627	N/A	76628	76629	76630
Purple	76631	N/A	76632	76633	76634
Orange	76635	N/A	76636	76637	76638
Green	76639	N/A	76640	76641	76642
Brown	76643	N/A	76644	76645	76646
Black	76647	N/A	76648	76649	76650
Grey	76651	N/A	76652	76653	76654
Pink	76598	N/A	76599	76600	76601
Tan	76602	N/A	76603	76604	76605
Light Blue	76606	N/A	76607	76608	76609
Ochre	97728	N/A	97739	97740	97741
Sky Blue	97742	N/A	97743	97744	97745



Repositionable Vinyl Tape (B – 581) – 100 ft./roll

Color	4" Wide Part No.	2.25" Wide Part No.	1.125" Wide Part No.	0.5" Wide Part No.
White	76697	76698	76699	76700
Yellow	76701	76702	76703	76704



Magnetic Supply* (B – 509) – 25 ft./roll

Color	4.25" Wide Part No.	2.5" Wide Part No.	1.125" Wide Part No.
White	76686	76687	N/A
Yellow	76688	76689	N/A



Tag Stock Supply Non-Adhesive* (B – 551) – 50 ft./roll

Color	4.25" Wide Part No.	3.25" Wide Part No.	2.5" Wide Part No.
White	76714	76715	76716

Meets OSHA 50 lb. pull test requirement.



Static Cling Supply* (B – 515) – 50 ft./roll

Color	4" Wide Part No.	2.25" Wide Part No.	1.125" Wide Part No.
Clear	76690	N/A	N/A



Phosphorescent Glow-in-Dark Tape* (B – 582) – 50 ft./roll

Color	4" Wide Part No.	2.25" Wide Part No.	1.125" Wide Part No.
Phosphorescent	76711	76712	76713



Phosphorescent Glow-in-Dark Tape* (B – 526) – 50 ft./roll

Color	4.25" x 50 ft. Part No.	2.5" x 50 ft. Part No.	1.375" x 50 ft. Part No.
Phosphorescent	105909	105910	105911



Reflective Tape* (B – 584) – 50 ft./roll

Color	4" Wide Part No.	2.25" Wide Part No.	1.125" Wide Part No.
Silver Reflective	76705	76706	76707
Yellow	96060	96061	96062



Specialty Tapes – 100 ft./roll

Color	4.25" Wide Part No.	2.5" Wide Part No.	1.375" Wide Part No.
White Cold Temperature* B549	76691	76692	76693
Yellow Cold Temperature* B549	76694	76695	76696
Gold Brushed Poly (50ft./roll) B575	76685	N/A	N/A
Metallized Poly* B565	76720	76721	7672

*These materials are not recommended for plotter cutting.



0

**BOILER MAKE-UP WATER
PUMP #501**

151-P501

Disconnect Location: Panel #59, Circuit #13



BREAKER #13
PUMP #501 (BOILER M.U. WTR)

⚠ WARNING

**Arc Flash Hazard.
Wear Appropriate PPE.
Death or Injury Can Result.**

(refer to NFPA 70E and 2002 NEC Article 110.16)

PANEL 59
Recovery Boiler Pumps
#127-160

**480 volts 3Phase
200 Amps**

Labels produced on GlobalMark®2 Industrial Label Maker and shown actual size.

REQUIRED
ON 2nd FLOOR
COMPOUND RM



***South Texas
Rental Centers***

Deer Park Texas, TX Branch
1-800-555-7000

I.D. No. 00408
18" CONCRETE SAW

Remarks: Perform
maintenance
Completion:
Removal may



Raw Material No.

Y99830



8" Mount Brackets (Galv.)



DANGER
DO NOT OPERATE
DO NOT REMOVE THIS TAG

This energy source has been LOCKED OUT

ID#: CMA-2 430266

Facility: Camden Road
 Location: Cell 135/140

Energy Source: E-1

Date & Time Locked Out: 7/24/2003 12:07:21 PM

This lock/tag may only be removed by:



Joe Brady
 performing routine quarterly preventive maintenance tasks
 may after 1st shift
 must in immediate discharge



OR-7 MED

← STEA

BRADY
 WHEN PERFORMANCE MATTERS MOST™

BRADY
 WHEN PERFORMANCE MATTERS MOST™

BRADY
 WHEN PERFORMANCE MATTERS MOST™

PREDICTIVE / PREVENTIVE MAINTENANCE ACTION

DATE	7/11/02	INITIALS	T. Woods
READING	8psi	ACTION	reset to 15psi

Increased Power.

Pair your GlobalMark2® Industrial Label Maker with one of these other Brady printers to give your labeling program even more power and options:

HandiMark® Portable Label Maker

On-the-spot ID with Brady HandiMark® Portable Label Maker

HandiMark® Portable Label Maker – perfect for smaller labels on-the-go. Portable operation, rugged construction in a hand-held size means HandiMark® Portable Label Maker goes where you go. Prints onto same B-588 industrial grade vinyl material as GlobalMark® Industrial Label Maker plus other materials too.

- Smaller signs, labels and pipe markers
- Output up to 2" wide
- Prints one color on a label
- Prints on B-588 vinyl plus reflective, repositionable, and tamper-resistant tapes
- 14 tape colors, 7 print ribbon colors
- Portable or AC power operation
- Built-in industrial symbols
- Option PC-operation with Brady MarkWare™ Facility Identification Software



Description	Part No.
HandiMark® Portable Label Maker	42001
PowerMark® Sign & Label Printer	13500

PowerMark® Sign & Label Printer

When it needs to be BIG, rely on the PowerMark® Sign & Label Maker

The best choice for making larger signs and labels that need to be viewed from a greater distance. Also prints multiple colors on a single label! Creates 10" x 14" signs, roll-form pipe markers and large labels up to 10" wide. Mount your PowerMark® Sign and Label Printer output to a rigid plastic or aluminum sign panel using the BLS1255 laminator!

- Output from 4" to 10" wide
- Prints single color or multiple colors on a single label
- Prints on B-580 outdoor grade vinyl tape, plus polyester, tag stock, reflective, and glow-in-the-dark materials
- 13 tape colors, 8 solid print ribbon colors, 14 multi-color print ribbon options
- Built-in industrial symbols
- Stand-alone operation or, PC-operation with optional Brady MarkWare™ Facility Identification Software



We've taken the stress out of setting up your new printer and software... and best of all, it's FREE! With Brady's Stress FREE System Setup, a member of the Brady Technical Support Team will walk you through the set-up of your GlobalMark 2 printer and software. **Call us today to schedule your FREE phone appointment at 1-800-643-8766, select Menu Option 4.**



Brady Worldwide, Inc.
6555 W. Good Hope Road
Milwaukee, WI 53223
1-888-272-3946
www.bradyid.com

Brady Canada
355 Apple Creek Blvd.
Markham, ON L3R 9X7
1-800-263-6179
www.bradycanada.com