

DIMENSIONAL SPECIFICATIONS

Overall Dimensions:

Nominal Dimension: 60" x 24" x 29-1/2" (W-D- H)

Actual Dimension: 59-15/16" x 23-7/8" x 29-7/8" (W-D- H)

Pedestals (Outside Dimensions with Drawer Front):

Letter Width Credenza: 14-7/8" x 19-7/16" x 17-3/4" (W-D- H)

Drawer (Inside Dimensions):

Letter Width Credenza Box: 12-1/4" x 14-13/16" x 4-1/16" (W-D-H)

Letter Width Credenza File: 12-1/4" x 16-13/16" x 10-1/2" (W-D-H)

Knee Space Between Pedestals:

27-7/8" x 19-19/64" x 28-1/8" (W-D-H)

MATERIAL SPECIFICATIONS

Top:

- 1-1/8" thick particleboard with Kraft Backer surface bottom and high-pressure laminate (HPL) top cover.
- Top dimensions – 59-15/16" x 23-7/8" (W-D)
- Top end caps: solid hardwood

End Panels:

- 1-1/8" thick particleboard with melamine surface back, high-pressure laminate (HPL) top cover, and .8mm edge trim on bottom.
- End panel dimensions – 23-7/8" x 28-1/8" (W-H)

Full Height Skirt:

- 3/4" particleboard with melamine both front and back.
- Skirt dimensions – 57-19/32" x 28-7/32" (W-H)

Inside Panel:

- 3/4" particleboard with melamine both front and back.

Grommet:

- There are two grommets that are located in the back corners of the desk. They are rectangle in shape. They are 1-7/8" from either side of the desk and 16-7/8" from the front edge of the desk.
- Size: 3-1/4" x 1-7/8" (W-H)

Box Drawer Material:

- **FRONTS**-3/4" thick particleboard with melamine both front and back .5mm PVC edgebanding on both sides and top.
- **SIDES**-7/16" thick fiberboard, 3-5/8" high.
- **BACK** 7/16" thick fiberboard, 2-1/16" high.
- **BOTTOM**-3/16" thick printed hardboard.
- **SUBFRONT**-7/16" thick fiberboard, 3-5/8" high.
- **CONSTRUCTION**-Sides mortise/tenon into drawer front, stapled to back and subfront at corners. Bottom fits into slots on sides.

File Drawer Material:

- **FRONTS**-3/4" thick particleboard with melamine both front and back .5mm edgebanding on both sides and top.
- **SIDES**- 7/16" thick fiberboard, 9-1/2" high.
- **BACK**- 7/16" thick fiberboard, 9-1/2" high.
- **BOTTOM**-3/16" thick printed hardboard.
- **SUBFRONT**-7/16" thick fiberboard, 9-1/2" high.
- **CONSTRUCTION**-Sides mortise/tenon into drawer front, stapled to back and subfront at corners. Bottom fits into slots on sides.

Hardware:

Hangrail Pack-262-4100

Product Pack-262-3124

MODEL FEATURES

- 3-1/2" Approach Side Top Overhang
- 3/4" Adjustable Glides
- 3/4" Extension Ball Bearing Box Drawer Slide
- Full Extension ball Bearing File Drawer Slide
- **File Drawer:** Letter and legal width side to side filing, letter width front to back filing. Hangrails are provided for all file drawers. Use Hanging folders with a maximum height of 9-3/4".
- **Lock ASSY #:** 50-5575
- **10500** Series wood produce meets or exceeds **ISTA** shipping and **ANSI/BIFMA X5.5** (latest Rev.) testing requirements for office furniture.
- ***Classical contemporary styling with hardwood accents.

PARTICLEBOARD: All particleboard is ANSI grade IM3 or better.



10700 Series H10765 Technical Specifications

CARTONING INFORMATION

Carton-Outside Dimensions: 62-1/2" x 26-1/2" x 31"

Cubes: 29.71

Carton #: 242-6211

Weight: 229lb