

# PIG® Extra-Duty Absorbent Mat Pad in Dispenser Box

#MAT174 - Heavy-weight • 16" x 20" • 50 pads



With additional top and bottom layers for extra toughness, PIG Extra-Duty Mat is highly abrasion resistant so it won't rip, tear, or fray.

- Special spunbond outer layers resist ripping and fraying from wiping rough surfaces or parts that would shred conventional mats
- No matter how you use it, this mat builds on the proven eight-layer, 100% polypropylene construction of PIG Mat, the strongest mat on the market!
- Exclusive dimple pattern speeds wicking of liquid throughout mat for faster, easier cleanup
- Highly absorbent, fine-fiber construction won't leave behind liquids or fiber residue
- Absorbs most common industrial liquids - oils, water, solvents, coolants and more; absorbs everything, works everywhere; that's why more plants worldwide use PIG Mat than any other brand
- Absorbed leaks and drips blend right in; dark gray color hides grime so mat stays on the job longer
- Low-lint for wiping rough parts or equipment and for cleaning in paint booth applications; also great for lining benches for rough or sharp parts
- Flame-resistant material won't burn immediately like cellulose mats; melts when exposed to high heat while on the job
- Dispenser box makes it easy to take, carry and store your mat while protecting it from dirt and moisture
- Perforated pads are ideal for wiping or tearing to size for cleanups
- Heavy-weight construction delivers greater durability and absorbency for demanding tasks and large-volume cleanups

Always in stock. Ships within 24 hours.



**New Pig**

By Phone:  
**1-855-493-HOGS**

Online:  
**newpig.com**

Email:  
**hothogs@newpig.com**

One Pork Avenue • Tipton PA 16684-0304

© 2014 New Pig Corporation. All rights reserved.  
PIG and the PIG logo are trademarks in the U.S. and other countries.

ITEM: MAT174 - Pg 1 of 2

# MAT174 Specifications

<b>Color:</b>	Dark Gray
<b>Dimensions:</b>	16" W x 20" L
<b>Mat Weight:</b>	Heavy-weight
<b>Fluids Absorbed:</b>	Oils, Coolants, Solvents & Water
<b>Recycled Content:</b>	40% Recycled Content
<b>Absorbency:</b>	Up to 9 gal. per box
<b>Absorbency per:</b>	Up to 23.04 oz. per pad
<b>Dispenser:</b>	Yes
<b>Perforated:</b>	Centered Widthwise
<b>Poly-Backing:</b>	No
<b>UV Resistant:</b>	No
<b>Sold as:</b>	50 pads per box
<b>Weight:</b>	8 lbs.
<b># per Pallet:</b>	30
<b>Composition:</b>	100% Polypropylene
<b>UNSPSC:</b>	47131901

# Technical Information

## Warnings & Restrictions:

There are no known warnings and restrictions for this product.

## Regulations and Compliance:

29 CFR 1910.22(a)(2) - Floors in the workplace should be, "maintained in a clean and, so far as possible, a dry condition."

## Technical Documents:

(Available at [newpig.com](http://newpig.com))

Product Data Sheet (PDS)

Safety Data Sheet (SDS)

Chemical Compatibility (CCG)



# MAT174 Metric Equivalent

<b>Dimensions:</b>	40.6cm W x 50.8cm L
<b>Absorbency:</b>	Up to 34.1 L per box
<b>Absorbency per:</b>	Up to 681.3 mL per pad
<b>Weight:</b>	3.6 kg



**New Pig**

By Phone:  
**1-855-493-HOGS**

Online:  
**newpig.com**

Email:  
**hothogs@newpig.com**