

Nilfisk GWD 255 Drum-Top Vacuum



Designed to meet the general plant cleaning and maintenance needs of industrial manufacturers, the **Nilfisk GWD 255 wet/dry drum-top vacuum** is powered by two independent bypass motors and can fit both 30 and 55 gallon drums, allowing users to recycle drums that are abundant in nearly every production plant.

- Washable main sack filter extends filter life
- Fifty-foot yellow safety cord for ultimate safety
- An optional float chamber and washable cartridge filter allows the GWD 255 to pick up both wet and dry materials
- Upstream HEPA filter available for pick-up of hazardous materials, ensuring 99.97% of particles are retained, down to 0.3 microns
- 38 mm or 50 mm accessory kits are available to meet a wide range of cleaning needs

For more information, contact our customer service department at 1-800-645-3475 or visit www.NilfiskIndustrialVacuums.com.

Nilfisk GWD 255

Drum-Top Vacuum



Specifications

Data	Units	GWD 255
Voltage @ 60Hz	volts	110-120
Power	watts	1800
Current Draw	amps	2
Waterlift, max	inches of H2O	80
Airflow, max	cfm	220
Cord Length	feet	50
Filter Efficiency, HEPA	DOP-tested	99.97% @ 0.3 microns

*Specifications are subject to change without notice / drum and trolley sold separately.



Nilfisk-Advance America, Inc., 740 Hemlock Road, Suite 100, Morgantown, PA 19543

Tel: 800.645.3475 • www.NilfiskIndustrialVacuums.com • Questions@nilfisk.com