



PROTECTIVE INDUSTRIAL PRODUCTS

19-D320 Specification Sheet

GLOVES MADE WITH DYNEEMA® DIAMOND TECHNOLOGY

PRODUCT DESCRIPTION:

G-Tek® 36X®, 13 gauge, gray & black Dyneema® Diamond Technology/Nylon/Lycra® seamless liner glove, gray polyurethane coated palm and finger tips, medium weight.

- Washable, resistant to chemicals, water and ultraviolet light.
- Seamless construction.
- Color coded hems for easy size identification.
- Silicone-free.
- Dyneema® is a brand of polyethylene fibers that are 10 to 15 times stronger than steel, more durable than polyester and a strength that is 40% greater than aramid fiber.

Applications:

Used for electronics, glass cutting, metal handling, food processing and meat processing.

TECHNICAL DATA:

Material: Dyneema® Diamond Technology, Nylon, Lycra®, polyurethane

Color: Salt & pepper blend

Cuff Style: Continuous knit

Available Sizes: XS - XXL

Packaging: 1 pair per bag, 12 pairs per dozen, 12 dozen per case

Case Dimensions (cm): 56 x 32 x 36 / (in): 22.0 x 12.6 x 14.2

Case Weight: (S) 15.6 lbs / 7.1 kg (L) 16.8 lbs / 7.6 kg
(M) 16.2 lbs / 7.3 kg (XL) 19.2 lbs / 8.7 kg
(XXL) 19.8 lbs / 9.0 kg

Manufacturer Certifications: ISO9001:2000 certified

Country of Origin/Harmonization Code: China/6116.10.6500

Laundering Instructions:

Recommend washing gloves in slightly warm water not exceeding 40° C. A mild non-ionic detergent should be used. A 5-10 minute cycle time should be employed. Tumble dry on low - maximum temperature 140° F (60° C)

PERFORMANCE PROPERTIES:

ASTM F1790-05: 1,246 grams +/- 10%

EN388: 4442


Abrasion	0	1	2	3	4	5
Cut	0	1	2	3	4	5
Tear	0	1	2	3	4	
Puncture	0	1	2	3	4	



DIMENSIONS:

Size Available	XS	S	M	L	XL	XXL
Over Length (cm) – A (in)	22.0 8.7	23.0 9.1	24.0 9.4	25.0 9.8	26.0 10.2	27.0 10.6
Palm Width (cm) – B (in)	8.5 3.3	9.0 3.5	9.5 3.7	10.0 3.9	10.5 4.1	10.5 4.1

Hem Color	Purple	Red	Yellow	Brown	Black	Sky Blue
Cuff Yarn Color	White	Green	Red	Yellow	Gray	White



BARCODE #	DOZEN	CASE
19-D320/XXL	01616314095909	02616314095908
19-D320/XL	01616314095886	02616314095885
19-D320/L	01616314095855	02616314095854
19-D320/M	01616314095862	02616314095861
19-D320/S	01616314095879	02616314095878
19-D320/XS	01616314095893	02616314095892

This document is the property of PIP and the information contained herein is proprietary to PIP.