

T2020152101-000 ✓ ACTIVE

HDC | HDC HD

TE Internal #: T2020152101-000

Rectangular Contact Inserts, Pin, 15+PE, Crimp Terminal, 15
Position, 26 – 14 AWG Wire Size, Power & Signal, HDC HD

[View on TE.com >](#)



Connectors > Rectangular Connectors > Rectangular Contact Inserts



Contact Type: **Pin**

Contact Insert Pole Configuration: **15+PE**

Termination Method to Wire & Cable: **Crimp Terminal**

Number of Positions: **15**

Sealable: **No**

Features

Product Type Features

Product Type	Insert
Sealable	No

Configuration Features

Number of Positions	15
---------------------	----

Contact Features

Contact Type	Pin
Contact Insert Pole Configuration	15+PE

Termination Features

Termination Method to Wire & Cable	Crimp Terminal
------------------------------------	----------------

Dimensions

Wire Size	26 – 14 AWG
-----------	-------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC

Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2022 (224)

Candidate List Declared Against: JUNE 2022 (224)

Does not contain REACH SVHC

Halogen Content

Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free

Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # T3609200102-000
DLX-20-MTE Part # T2020001025-000
CDM-2.5TE Part # T1319100125-000
H10A-TS-M25TE Part # T1010031100-000
H3A-KDTPTE Part # T2020152201-000
HD-015-FTE Part # T2020153201-000
HD-015-FJAlso in the Series | **HDC HD**



Connector Contacts(24)



Insertion & Extraction Tools(5)



Rectangular Contact Inserts(43)

Documents

Product Drawings

[HD-015-M](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_T2020152101-000_B.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_T2020152101-000_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_T2020152101-000_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Heavy Duty Connectors](#)

English

[HEAVY DUTY CONNECTORS](#)

English

Product Specifications

[Application Specification](#)

English

Agency Approvals

[Agency Approval Document](#)

English