



MR16 LED

7MR16/S15 3000 DIM AF 10/1

Philips MR16 Dimmable LED Lamps provide ambient level light to illuminate hard to maintain applications. Increased transformer compatibility allows for operation on a wider range of transformers. Available in dimmable and non-dimmable versions, these lamps are ideal for track and open recessed fixtures in retail, hospitality and residential spaces.

Product data

• General Characteristics

Cap-Base	GU5.3
Bulb	MR16 [MR 16inch/50mm]
Rated Avg. Life (Hours)	40000 hr
Nominal Lifetime hours	40000 hr

• Light Technical Characteristics

Color Code	830
Color Designation	White
Beam Angle	15 D
Beam Description	- [-]
Correlated Color Temperature	3000 K
Approximate Lumens	420 Lm
Approx. MBCP	3150 cd
CRI	80
Luminous Efficacy Lamp	60.00 Lm/W
Color Temp. (Kelvin)	3000 K [CCT 3000K]
Rated Luminous Flux	420 Lm
LLMF - end nominal lifetime	40000 %
Colour consistency	6 steps
Rated Beam Angle	15 D
Luminous flux in 90° cone	400 Lm

• Electrical Characteristics

Wattage	7 W
Wattage Technical	7 W
Voltage	12 V
Line Frequency	50-60 Hz
Power Factor	0.7 -

Lamp Current mA	715 mA
Dimmable	Yes
Wattage Equivalent	35 W
Rated Wattage	7.0 W
Starting Time	0.5 s
Warm-up Time to 60% Light Outp	instant full light
Suitable for accent lighting	Yes

• Temperature Characteristics

T-case maximum	110 C
----------------	-------

• Environmental characteristics

Energy Efficiency Label (EEL)	A
-------------------------------	---

• Measuring Conditions

Switching cycle	50000X
-----------------	--------

• Product Dimensions

Overall Length C	50 mm
Diameter D	54 mm

• Product Data

Product number	432666
Full product name	7MR16/S15 3000 DIM AF 10/1
Short product name	7MR16/S15 3000 DIM AF 10/1
Pieces per Sku	1
Skus/Case	10
Bar code on pack	46677432669
Bar code on case	50046677432664




PHILIPS

MR16 LED

Logistics code(s) 929000262804


eop_net_weight_pp 0.060 kg

Dimensional drawing



7MR16/S15 3000 DIM AF 10/1

Product	C (Norm)	C1 (Max)	D (Norm)	D1 (Norm)
LED D 7-35W 3000K MR16 15D	50	-	54	-



GU5.3



© 2014 Koninklijke Philips N.V. (Royal Philips)
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

www.philips.com/lighting

2014, April 8
data subject to change