



PAR30L LED Single Optic lamp with AirFlux Technology

12PAR30L/F25 2700 DIM AF SO 6/1

Philips PAR30L LED Retail Optic lamp with AirFlux Technology improves shopping experience with superior lighting aesthetics and optimal thermal efficiency in a sleek, lightweight design.

Product data

• General Characteristics

Cap-Base	E26
Bulb	PAR30L
Rated Avg. Life (Hours)	50000 hr

• Light Technical Characteristics

Color Code	WH
Color Designation	White
Beam Angle	25 D
Beam Description	25D [Medium beam]
Correlated Color Temperature	2700 K
Approximate Lumens	850 Lm
Approx. MBCP	5000 cd
CRI	80
Luminous Efficacy Lamp	70.83 Lm/W
Color Temp. (Kelvin)	2700 K [CCT 2700K]
Rated Luminous Flux	850 Lm

• Electrical Characteristics

Wattage	12 W
Wattage Technical	12 W
Voltage	120 V
Line Frequency	60 Hz

Power Factor	0.9 -
Lamp Current mA	113 mA
Dimmable	Yes
Wattage Equivalent	75 W
Starting Time	0.5 s

• Measuring Conditions

Switching cycle	20000X
-----------------	--------

• Product Dimensions

Overall Length C	116 mm
Diameter D	92 mm

• Product Data

Product number	430124
Full product name	12PAR30L/F25 2700 DIM AF SO 6/1
Short product name	12PAR30L/F25 2700 DIM AF RO 6/1
Pieces per Sku	1
eop_pck_cfg	6
Skus/Case	6
Bar code on pack	46677430122
Bar code on case	50046677430127
Logistics code(s)	929000251304
eop_net_weight_pp	0.240 kg

Warnings and Safety

- Suitable for use in damp locations.


- Not for use in totally enclosed luminaires.
- Before replacing, turn off power and let lamp cool to avoid electrical shock or burn.



PHILIPS

PAR30L LED Single Optic lamp with AirFlux Technology

Dimensional drawing



E26

12PAR30L/F25 2700 DIM AF SO 6/1

Product	C (Norm)	C1 (Max)	D (Norm)	D1 (Norm)
LED 12-75W E26 2700K 120V PAR30L 25D DIM	116	-	92	-



© 2014 Koninklijke Philips N.V. (Royal Philips)
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

www.philips.com/lighting

2014, April 8
data subject to change