




HDC

TE Internal #: T2050962101-007
Rectangular Contact Inserts, Pin, Pin, 48, Crimp Terminal, 48
Position, Wire & Cable, 26 – 12 AWG Wire Size, .14 – 4 mm² Wire
Size, 16 A

[View on TE.com >](#)

Connectors > Rectangular Connectors > Rectangular Contact Inserts > HDC HEEE RAIL COMPLIANT INSERT SERIES



Rectangular Connector Insert Type: **Pin**
Contact Type: **Pin**
Contact Insert Pole Configuration: **48**
Termination Method to Wire & Cable: **Crimp Terminal**
Number of Positions: **48**

[All HDC HEEE RAIL COMPLIANT INSERT SERIES \(20\)](#)

Features

Product Type Features

Product Type	Insert
Product Size	6
Rectangular Connector Insert Type	Pin
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	48
---------------------	----

Electrical Characteristics

Power Circuit Voltage	400 V
Power Circuit Current	16 A
Current Rating	16 A

Body Features

Color	Gray
-------	------



Contact Features

Contact Type	Pin
Contact Insert Pole Configuration	48
Contact Current Rating (Max)	16 A

Termination Features

Termination Method to Wire & Cable	Crimp Terminal
------------------------------------	----------------

Dimensions

Wire Size	.14 – 4 mm²
-----------	-------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Packaging Features

Packaging Method	Box
Packaging Quantity	5

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on



requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # T2050962201-007
HEEE-048-F 49-96



TE Part # T3609400102-000
DLX-40-M



TE Part # T1210320140-000
H32B-TS-M40



TE Part # T2030001040-000
CEM-4.0

Documents

Product Drawings

HEEE-048-M 49-96

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_T2050962101-007_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_T2050962101-007_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_T2050962101-007_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

EN45545 COMPLIANT HDC INSERTS

English

Product Specifications

Application Specification

English